# ZS4-BR



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products + Low Voltage Products and Systems + Connection Devices + Terminal Blocks + SNK Series

#### **General Information**

Extended Product Type: ZS4-BR

**Product ID**: 1SNK505064R0000 **EAN**: 3472595050642

Catalog Description: ZS4-BR Screw Clamp Terminal Block - Feed-through - Brown

Long Description: - Save space by connecting conductors up to 4 mm² (without insulated ferr

ule, CB certified) 12 AWG in just 5.2 mm 0.205 in spacing, - Perfectly adap

ted to solar applications: voltage is rated 1000 V AC / DC IEC.

#### Ordering

Color:	Brown
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

### Popular Downloads

Data Sheet, Technical Information:	1SNK161001D0201
Instructions and Manuals:	1SNK160027C0201

#### **Dimensions**

Product Net Width:	5.2 mm
Product Net Height:	53 mm
Product Net Length:	47.3 mm
Product Net Depth / Length:	47.3 mm
Product Net Weight:	8.8 g

#### **Technical**

Rated Cross-Section:	4 mm²
	7 11111
Spacing:	5.2 mm
Connection Type:	Screw clamp
Function:	Feed-through
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.22 4 mm²
	Screw Clamp / Flexible 2x 0.2 1.5 mm²
	Screw Clamp / Rigid 1x 0.2 4 mm²
	Screw Clamp / Rigid 2x 0.2 1.5 mm²
	Screw Clamp / With Insulated Ferrrule 1x 0.22 2.5 mm²

Screw Clamp / Without Insulated Ferrule 1x 0.22 ... 4 mm<sup>2</sup>

Screw Clamp / With Twin Ferrule 2x 0.22 ... 1.5 mm<sup>2</sup>

	40 B0
Gauge Type:	A3-B3
Rated Current (I <sub>n</sub> ):	Main Circuit 32 A
Rated Short-time Withstand Current (I <sub>cw</sub> ):	for 1 s 480 A
Rated Voltage (U <sub>r</sub> ):	1000 V
Rated Impulse Withstand Voltage $(U_{imp})$ :	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	1 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	10.5 mm
This Stripping Longtin.	10.5 11111
Recommended Screw Driver:	3.5 mm
Recommended Screw Driver: echnical UL/CSA Maximum Operating Voltage	3.5 mm
Recommended Screw Driver: echnical UL/CSA  Maximum Operating Voltage UL/CSA: Connecting Capacity Main Circuit	3.5 mm  Main Circuit 600 V  Screw Clamp / Flexible 1x 24 12 AWG Screw Clamp / Flexible 2x 24 16 AWG Screw Clamp / Rigid 1x 24 12 AWG Screw Clamp / Rigid 2x 24 16 AWG Screw Clamp / Rigid 2x 24 16 AWG Screw Clamp / With Insulated Ferrule 1x 24 14 AWG Screw Clamp / Without Insulated Ferrule 1x 24 12 AWG
Recommended Screw Driver: echnical UL/CSA  Maximum Operating Voltage UL/CSA: Connecting Capacity Main Circuit UL/CSA:	3.5 mm  Main Circuit 600 V  Screw Clamp / Flexible 1x 24 12 AWG Screw Clamp / Flexible 2x 24 16 AWG Screw Clamp / Rigid 1x 24 12 AWG Screw Clamp / Rigid 2x 24 16 AWG Screw Clamp / Rigid 2x 24 16 AWG Screw Clamp / With Insulated Ferrule 1x 24 14 AWG Screw Clamp / Without Insulated Ferrule 1x 24 12 AWG Screw Clamp / With Twin Ferrule 2x 24 16 AWG

### En

Operation -55 ... +110 °C **Ambient Air Temperature:** Storage -55 ... +110 °C Compliant Resistance to Vibrations acc. to IEC 60068-2-6:

**RoHS Status:** Following EU Directive 2002/95/EC August 18, 2005 and amendment

# Certificates and Declarations (Document Number)

**ATEX Certificate:** 1SND162004A1708 **BV Certificate:** 1SND161073A0204

CB Certificate:	1SND161017A0202
CSA Certificate:	1SND161070A0209
cUL Certificate:	1SND161040A0206
Declaration of Conformity - CE:	1SND225112U1004
DNV Certificate:	1SND161087A0202
EAC Certificate:	1SND161010A1100
Environmental Information:	1SND220071E1000
Instructions and Manuals:	1SNK160027C0201
RINA Certificate:	1SND161088A0200
RMRS Certificate:	1SND161008A1101
RoHS Information:	1SND230491F0206

# Classifications

Object Classification Code:	X
E-nummer:	2925907
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block

# **Container Information**

Package Level 1 Units:	50 piece
Package Level 1 Width:	54 mm
Package Level 1 Depth / Length:	252 mm
Package Level 1 Height:	52 mm
Package Level 1 Gross Weight:	0.44 kg
Package Level 1 EAN:	3472595050642
Package Level 2 Units:	900 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	400 mm
Package Level 2 Height:	200 mm
Package Level 2 Gross Weight:	7.92 kg
Package Level 3 Units:	43200 piece
Product Packing Type:	Вох

