

CGA2B3X7S1A474K050BE

TDK Item Description : CGA2B3X7S1A474KT***S




Equivalent C1005X7S1A474K for Automotive

Application & Main Feature

Automotive Grade (Soft Termination)

Series

CGA2(1005) [EIA CC0402]



Dimensions

L	1.00mm +0.15,-0.05mm
W	0.50mm +0.1,-0.05mm
T	0.50mm +0.1,-0.05mm
B	0.10mm Min.
G	0.30mm Min.

Temperature Characteristic

X7S (-55 to 125 degC +/-22%)

Rated Voltage

1A (10Vdc)

Capacitance

470nF

Capacitance Tolerance

K (+/-10%)

Dissipation Factor






7.5% Max.

Insulation Resistance

212Mohm Min.

AEC-Q200

Yes



Characterization Sheet (Multilayer Ceramic Chip Capacitors)



All specifications are subject to change without notice.

March 16, 2017