Product data sheet Characteristics

XS4P30PA370D

inductive sensor XS4 M30 - L70mm - PPS - Sn15mm - 12..48VDC - M12





Main

		;
Range of product	OsiSense XS	
Series name	General purpose	_ \
Sensor type	Inductive proximity sensor	_ o
Device application	-	-thes
Sensor name	XS4	_ \
Sensor design	Cylindrical M30	relia
Size	70 mm	<u> </u>
Body type	Fixed	Suitability
Detector flush mounting acceptance	Non flush mountable	- IS DU
Material	Plastic	- inimi
Type of output signal	Discrete	r dete
Wiring technique	3-wire	ed fo
[Sn] nominal sensing distance	15 mm	– sii eq
Discrete output function	1 NO	
Output circuit type	DC	 <u>v</u> .
Discrete output type	PNP	
Electrical connection	M12 male connector, 4 pins	_fat
[Us] rated supply voltage	1248 V DC with reverse polarity protection	-itsdi
Switching capacity in mA	<= 200 mA DC with overload and short-circuit protection	s
IP degree of protection	IP67 conforming to IEC 60529	ded

Complementary

Thread type	M30 x 1.5	
Detection face	Frontal	
Front material	PPS	
Enclosure material	PPS	
Operating zone	012 mm	

Differential travel	115% of Sr
Status LED	1 LED (yellow) for output state
Supply voltage limits	1058 V DC
Switching frequency	<= 1000 Hz
Voltage drop	<= 2 V (closed
Current consumption	010 mA (no-load)
Delay first up	<= 10 ms
Delay response	<= 0.3 ms
Delay recovery	<= 0.7 ms
Marking	CE
Threaded length	52 mm
Height	30 mm
Length	70 mm
Product weight	0.08 kg

Environment

Product certifications	CCC	
	CSA	
	UL	
Ambient air temperature for operation	-2570 °C	
Ambient air temperature for storage	-4085 °C	
Vibration resistance	25 gn, amplitude: +/- 2 mm (f = 1055 Hz) conforming to IEC 60068-2-6	
Shock resistance	50 gn (duration = 11 ms) conforming to IEC 60068-2-27	


Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0813 - Schneider Electric declaration of conformity
	Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold
	Reference not containing SVHC above the threshold
Product environmental profile	Available
	End of Life Information
Product end of life instructions	Available

Contractual warranty

o management of the control of the c		
Warranty period	18 months	

Dimensions




Product data sheet Mounting and Clearance

XS4P30PA370D


Minimum Mounting Distances

Side by side




e (1) ≥ 60 mm/2.36 in.


Face to face



e (2) \geq 180 mm/7.09 in. Facing a metal object



e (3) ≥ 45 mm/1.77 in. Mounted in a metal support



 $d \ge 90 \text{ mm/}3.54 \text{ in.}$ $h \ge 30 \text{ mm/}1.18 \text{ in.}$


XS4P30PA370D

Wiring Schemes

M12 connector



PNP




- (+) Not connected 1: 2:
- 3 : 4 :
- (-) NO Output

Product data sheet Performance Curves

XS4P30PA370D

Performance Curves

Standard Steel Target: 45x45x1 mm



- (1) (2) (y) Pick-up points
- Drop-out points (object approaching from the side)
- Sensing distance in mm