


ALC70, Aluminum Electrolytic, 150 uF, 20%, 450 VDC, -40/+85°C



General Information	
<b>Series:</b>	ALC70
<b>Dielectric:</b>	Aluminum Electrolytic
<b>Description:</b>	Snap-In, Aluminum Electrolytic
<b>RoHS:</b>	Yes
<b>Lead:</b>	2 Pin
<b>AEC-Q200:</b>	No
<b>Notes:</b>	Dimensions D And L Include Slewing
<b>Shelf Life:</b>	156 Weeks

Dimensions	
<b>D</b>	30mm +1mm
<b>L</b>	30mm +/-2mm
<b>S</b>	10mm +/-0.1mm
<b>LL</b>	6.3mm +/-1mm
<b>F</b>	2mm +/-0.1mm

Packaging Specifications	
<b>Weight:</b>	40 g
<b>Slewing:</b>	Yes
<b>Packaging:</b>	Bulk, Bag

Specifications	
<b>Capacitance:</b>	150 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	450 VDC, 495 VDC (Surge)
<b>Temperature Range:</b>	-40/+85°C
<b>Rated Temperature:</b>	85°C
<b>Life:</b>	13000 Hrs (Rated Voltage And Ripple Current At 85C), 21000 Hrs (Rated Voltage at 85C)
<b>Resistance:</b>	920 mOhms (100Hz 20C), 512 mOhms (10kHz 20C)
<b>Ripple Current:</b>	1.16 Amps (100Hz 85C), 2.98 Amps (10kHz 85C)
<b>Leakage Current:</b>	405 uA (5min 20°C)