Detector Switch

multicomp PRO

RoHS

Compliant



Features

- · Noiseless switching system
- Long travel
- Vertical Push Type
- Sealed type
- · Halogen free

Applications

- Automotive
- · Industrial equipment
- White goods

Specifications

Contact Rating : 10mA, $\leq 25\text{V DC}$ ($680\Omega \pm 1.5\%$) Contact Resistance : $680\Omega \pm 1.5\%$ (free position) 8.3mm to 9.15mm ($3380\Omega \pm 1.5\%$)


6.85mm to 8mm (\leq 500m Ω)

*Insulation Resistance : $100M\Omega$ min. 500V DC *Dielectric Strength : 250V AC/1 minute Operating Force : Actuating Force $\leq 1.6N$

Operating Life : 2,00,000 cycles
Operating Temperature : -40°C to +85°C
Storage Temperature : -40°C to +85°C


* Only for without resistors type.

Diagram



Dimensions: Millimetres

Circuit



Part Number Table

Description	Part Number
Detector Switch, 10mA, 25V DC, SPST, Wire Lead	MP000736
Detector Switch, Lever, 10mA, 25V DC, SPST, Wire Lead	MP000737

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

