



Energizer® Vision HD+ Headlight

The Energizer® Vision HD+ headlight is another innovative headlight solution within the Energizer® premium headlight line. With the latest LED technology, users get a bright, lightweight hands-free solution with ample run time capability. Patented optics offer exceptional direct and peripheral vision, making the Energizer® Vision HD+ a perfect light for home, work and outdoor activities. With the advanced dimming feature, users can control the intensity of light from 100% to 10%. Consumers also enjoy the Next Push Off™ technology to avoid unnecessary switch cycles. With an adjustable head strap, water resistant design and pivoting head to direct light exactly as needed, this headlight is another way Energizer® continues to deliver innovative lighting solutions.

Design Benefits

- ✓ Red LED mode allows users to preserve night vision
- ✓ Advanced dimming feature to control light intensity in multiple modes:
 - ✓ Spot + Flood
 - ✓ Spot
 - ✓ Flood
- ✓ Pivoting head to direct light where needed
- ✓ IPX4 water resistant and shatterproof lens construction

Performance Benefits

- ✓ Latest LED technology and patented optics, delivering exceptional vision
- ✓ Up to 4X brighter than standard LED technology

Light and Power Source

- ✓ Features LED technology
- ✓ Operates on 3AAA batteries
 - ✓ (Includes 3AAA Energizer MAX® batteries)



--	--	--	--	--

5 Operating Modes + Dimming Feature					
Mode	Lumens	Runtime	Beam Distance	Impact Resistant	Water Resistant
Red	-	20hrs	-	1m	IPX4
Spot + Flood - High	250	7hrs	70m	1m	IPX4
Spot + Flood - Low	30	50hrs	-	1m	IPX4
Spot - High	180	8hrs	-	1m	IPX4
Flood - High	80	22hrs	-	1m	IPX4