

Han M23 HBM front male M20x1,5



| | |
|--------------------|---|
| Part number | 09 15 100 0363 |
| Specification | Han M23 HBM front male M20x1,5 |
| HARTING eCatalogue | https://b2b.harting.com/09151000363 |

Identification

| | |
|-----------------------------|---------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han® M23 Signal |
| Type of hood/housing | Bulkhead mounted housings |
| Description of hood/housing | Front mounting |

Version

| | |
|--------------|---|
| Locking type | Screw locking |
| Size | M23 |
| Fixing | Thread M20 x 1.5 |
| Details | for male inserts Not compatible to ComLock |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP67 in locked position IP69 / IPX9K acc. to ISO 20653 in locked position |

Material properties

| | |
|-----------------------------|--|
| Material (hood/housing) | Copper-zinc alloy |
| Surface (hood/housing) | Nickel plated |
| Material (seal) | NBR |
| Colour (seal) | Black |
| RoHS | compliant with exemption |
| RoHS exemptions | 6c: Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |



Pushing Performance

Material properties

| | |
|-----------------------|------|
| REACH SVHC substances | Lead |
|-----------------------|------|

Specifications and approvals

| | |
|----------|-----------------------|
| UL / CSA | UL 1977 ECBT2.E235076 |
|----------|-----------------------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 5 |
| Net weight | 32.9 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| eCl@ss | 27440202 Shell for industrial connectors |