Transient Voltage Suppression Diode SMBJ Series, 600 Watts



RoHS Compliant



Features

- · For surface mounted applications
- Reliable low cost construction utilizing molded plastic technique
- · Plastic material has UL recognition 94V-0
- Typical IR less than 1µA above 10V
- Fast response time: typically less than 5.0ns fo Bi-direction, from 0 Volts to BV min

Mechanical Data

- · Case: Molded Plastic
- · Polarity: By cathode band denotes bi-directional device
- · Weight: 0.003 ounces, 0.093 grams

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

Characteristics	Symbol	Value	Unit	
Peak Power Dissipation at T _A = 25°C by 10×1000μs waveform (Note 1), (Note 2)	Рррм	600	W	
Peak Forward Surge Current 8.3ms Single Half Sine-Wave Super Imposed on Rated Load (JEDEC Method)	IFSM	100	А	
Steady State Power Dissipation at T _L = 75°C	PM(AV)	5	W	
Typical Thermal Resistance Junction to Lead	Reja	20	°C/W	
Typical Thermal Resistance Junction to Ambient	Rejl	100	°C/W	
Operating Temperature Range	TJ	55 to 1150	°C	
Storage Temperature Range	Tstg	-55 to +150		

Notes:

- 1. Non-repetitive current pulse, per Fig. 3 and derated above TA = 25°C per Fig. 1.
- 2. Thermal Resistance junction to Lead.
- 3. The typical data above is for reference only.

Part Number		Reverse Stand off Voltage VR	Breakdown Voltage VBR (Volts) @ Ιτ		Test Current I _T	Max. Clamping Voltage VC @ IPP	Max. Peak Pulse Current	Max. Reverse Leakage IR@ VR
Unidirectional	Bidirectional	V _R (V)	Min. (V)	Max. (V)	l⊤ (mA)	Vc (V)	IPP (A)	IR (μ A)
-	SMBJ6.8CA	6.8	7.56	8.35	10	11.7	51.3	400

Notes:

- 1. For bidirection type having VRWM of 10 volts and less,the IR limit is double.
- 2. For parts without A(VBR is ±10% and Vc is 5% higher than with A parts).


Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands





Transient Voltage Suppression Diode SMBJ Series, 600 Watts





Ratings and Characteristic Curves
















Diagram

SMB (DO-214AA)





Part Number Table

Description	Part Number	
Transient Voltage Suppression Diode, SMBJ Series, Bidirectional, 600W, DO-214AA	SMBJ6.8CA	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands



Page <2> 04/09/19 V1.0