

# M12 panel feedtrough/PCB straight A-cod.



Part number	21 03 321 1520
Specification	M12 panel feedtrough/PCB straight Acod.
HARTING eCatalogue	https://b2b.harting.com/21033211520

#### Identification

Category	Connector
Series	Circular connectors M12
Element	PCB adapter
Specification	Straight

#### Version

Termination method	Reflow soldering termination (THR/SMC)
Gender	Male
Locking type	Screw locking
Shielding	Shielded
Number of contacts	5
Coding	A-coding

#### Technical characteristics

Rated current	4 A
Rated voltage	50 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Insulation resistance	> 10 <sup>8</sup> Ω
Contact resistance	≤10 mΩ
Ambient temperature	-40 +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP67
Overvoltage category	III



#### Technical characteristics

Isolation group	I (600 ≤ CTI)	
-----------------	---------------	--

## Material properties

Material (insert)	Polyamide
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
Material (hood/housing)	Zinc die-cast
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	IEC 61076-2-101	
----------------	-----------------	--

# Commercial data

Packaging size	10
Net weight	23.5 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440402 PCB connector