

International Rectifier

Ultrafast Rectifier

MURS120PbF

Features

- Ultrafast Recovery Time
- Low Forward Voltage Drop
- Low Leakage Current
- 175°C Operating Junction Temperature
- Lead-Free ("PbF" suffix)

$I_{F(AV)} = 1.0\text{Amp}$
 $V_R = 200\text{V}$

Description/ Applications

International Rectifier's MUR.. series are the state of the art Ultra fast recovery rectifiers specifically designed with optimized performance of forward voltage drop and ultra fast recovery time.

The planar structure and the platinum doped life time control, guarantee the best overall performance, ruggedness and reliability characteristics.

These devices are intended for use in the output rectification stage of SMPS, UPS, DC-DC converters as well as free-wheeling diode in low voltage inverters and chopper motor drives.


Their extremely optimized stored charge and low recovery current minimize the switching losses and reduce over dissipation in the switching element and snubbers.

Absolute Maximum Ratings

Parameters	Max	Units
V_{RRM} Peak Repetitive Peak Reverse Voltage	200	V
$I_{F(AV)}$ Average Rectified Forward Current, $T_L = 158^\circ\text{C}$	1	A
I_{FSM} Non Repetitive Peak Surge Current	40	
T_J, T_{STG} Operating Junction and Storage Temperatures	- 65 to 175	$^\circ\text{C}$

Case Styles

MURS120PbF



Cathode Anode

SMB

Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

Parameters	Min	Typ	Max	Units	Test Conditions
V_{BR}, V_r Breakdown Voltage, Blocking Voltage	200	-	-	V	$I_R = 100\mu\text{A}$
V_F Forward Voltage	-	0.83	0.875	V	$I_F = 1\text{A}$
	-	0.65	0.71	V	$I_F = 1\text{A}, T_J = 150^\circ\text{C}$
I_R Reverse Leakage Current	-	0.1	2	μA	$V_R = V_R$ Rated
	-	11	50	μA	$T_J = 150^\circ\text{C}, V_R = V_R$ Rated
C_T Junction Capacitance	-	12	-	pF	$V_R = 200\text{V}$

Dynamic Recovery Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

Parameters	Min	Typ	Max	Units	Test Conditions
t_{rr} Reverse Recovery Time	-	-	35	ns	$I_F = 1.0\text{A}, dI_F/dt = 50\text{A}/\mu\text{s}, V_R = 30\text{V}$
	-	-	25		$I_F = 0.5\text{A}, I_R = 1.0\text{A}, I_{REC} = 0.25\text{A}$

Thermal - Mechanical Characteristics

Parameters	Min	Typ	Max	Units
T_J Max. Junction Temperature Range	-	-	175	°C
T_{Stg} Max. Storage Temperature Range	-65	-	175	
R_{thJL} Thermal Resistance, Junction to Lead	-	-	21	°C/W
Wt Weight		-	0.1	g
		-	0.07	(oz)
wt Approximate Weight	0.10 (0.003)			g (oz.)
Case Style	SMB			
Device Marking	IRU120			




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 2 - Typical Values Of Reverse Current Vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance Vs. Reverse Voltage




Fig. 4 - Max. Thermal Impedance Z_{thJC} Characteristics




Fig. 5 - Max. Allowable Lead Temperature Vs. Average Forward Current







Fig. 6 - Forward Power Loss Characteristics

Fig. 7 - Typical Reverse Recovery vs. di_F/dt Fig. 8 - Typical Stored Charge vs. di_F/dt


(3) Formula used: $T_C = T_J - (P_d + P_{d_{REV}}) \times R_{thJC}$;
 $P_d = \text{Forward Power Loss} = I_{F(AV)} \times V_{FM} @ (I_{F(AV)} / D)$ (see Fig. 6);
 $P_{d_{REV}} = \text{Inverse Power Loss} = V_{R1} \times I_R (1-D)$; $I_R @ V_{R1} = \text{rated } V_R$

Outline Table




Marking & Identification

Each device has 2 rows for identification. The first row designates the device as manufactured by International Rectifier, indicated by the letters "IR", and the Part Number (indicates the current, the voltage rating and Schottky Generation). The second row indicates the year, the week of manufacturing and the Site ID.



Tape & Reel Information



Ordering Information Table

Device Code		MUR	S	1	20	TR	PbF
		(1)	(2)	(3)	(4)	(5)	(6)
1	-	Ultrafast MUR Series					
2	-	Package Style: SMB					
3	-	Current Rating (1 = 1A)					
4	-	Voltage Rating (20 = 200V)					
5	-	• none = Box (1000 pieces)					
		• TR = Tape & Reel (3000 pieces)					
6	-	• none = Standard Production					
		• PbF = Lead-Free					

Data and specifications subject to change without notice.
 This product has been designed and qualified for Industrial Level and Lead-Free.
 Qualification Standards can be found on IR's Web site.

 International
 Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
 TAC Fax: (310) 252-7309
 Visit us at www.irf.com for sales contact information. 11/04