



Main

Range of product	Harmony XB4 Harmony XB5
Product or component type	Contact block
Device short name	ZBE
Sale per indivisible quantity	1
IP degree of protection	IP20 IEC 60529
Contacts type and composition	2 NC
Contact operation	Slow-break
Contact block type	Double
Contacts usage	High power switching contacts
Connections - terminals	Screw clamp terminals $\leq 1 \times 2.5 \text{ mm}^2$ with cable end Screw clamp terminals $\leq 2 \times 1.5 \text{ mm}^2$ with cable end Screw clamp terminals $\leq 2 \times 2.5 \text{ mm}^2$ without cable end Screw clamp terminals $\geq 1 \times 0.5 \text{ mm}^2$ without cable end

Complementary

Product weight	0.032 kg
Positive opening	With
Mechanical durability	10000000 cycles
Short-circuit protection	10 A cartridge fuse gG EN/IEC 60947-5-1
[Ith] conventional free air thermal current	10 A EN/IEC 60947-5-1
[Ui] rated insulation voltage	300 V EN 60947-1
[Uimp] rated impulse withstand voltage	6 kV EN 60947-1
[Ie] rated operational current	1.1 A 125 V DC-13 P300 EN/IEC 60947-5-1
Mounting of block	Front mounting
Condition of use	Mounting on push-button collar
Electrical composition code	C15 1
Compatibility code	ZBE

Environment

Ambient air temperature for storage	-40...70 °C
-------------------------------------	-------------

Ambient air temperature for operation	-40...70 °C
Vibration resistance	5 gn 2...500 Hz IEC 60068-2-6
Shock resistance	30 gn 18 ms half sine wave acceleration IEC 60068-2-27 50 gn 11 ms half sine wave acceleration IEC 60068-2-27

Contractual warranty

Warranty period	18 months
-----------------	-----------