



Main

Range of product	Phaseo Rectified
Product or component type	Power supply
Power supply type	Rectified and filtered
Rated power in W	960 W
Input voltage	400 V AC three phase, terminal(s): L1, L2, L3
Output voltage	24 V DC
Power supply output current	40 A
Operating position	Horizontal at 40 °C Vertical at 55 °C

Complementary

Input voltage limits	360...440 V
Network frequency limits	47...63 Hz
Input voltage tolerance	+/- 20 V
Inrush current	30 A at 400 V
Cos phi	0.857 at 400 V
Efficiency	78 %
Power dissipation in W	211 W
Holding time	5 ms
Output protection type	Against overload and short-circuits, protection technology: external fuse, 50 A Against overvoltage, protection technology: 2 J peak limiter
Connections - terminals	Screw type terminals for input ground connection, connection capacity: 1 x 2.5...1 x 4 mm ² AWG 14...AWG 11 Screw type terminals for input connection, connection capacity: 9 x 2.5...9 x 4 mm ² AWG 14...AWG 11 Screw type terminals for output connection, connection capacity: 4 x 16 mm ² AWG 6
Marking	CE
Fixing mode	By 4 screws
Output coupling	Parallel Series
Operating altitude	3000 m
Name of test	Conducted/radiated emissions conforming to EN 55011 class B Electrostatic discharges conforming to EN/IEC 61000-4-2 Emission conforming to EN 50081-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Emission conforming to EN 61000-6-3
Rapid transient conforming to IEC 61000-4-4
Surge conforming to EN/IEC 61000-4-5

Status LED	1 LED green for output voltage
Depth	140 mm
Height	310 mm
Width	310 mm
Product weight	17.5 kg


Environment

Product certifications	cULus UL 508 EAC KC
Environmental characteristic	EMC conforming to EN/IEC 61000-3-2 EMC conforming to IEC 62041 Safety conforming to EN/IEC 61558-2-6 Safety conforming to UL 508 Safety conforming to UL 60950-1
IP degree of protection	IP20 conforming to EN/IEC 60529
Ambient air temperature for operation	-20...55 °C
Ambient air temperature for storage	-40...80 °C
Relative humidity	0...95 % without condensation or dripping water
Electrical shock protection class	Class I conforming to VDE 0106-1
Dielectric strength	2000 V between input and ground 4600 V between input and output 500 V between output and ground

Contractual warranty

Warranty period	18 months
-----------------	-----------

Dimensions




Dimensions in mm

a	b	c	G	J	Ø
310	310	140	260	95	11


Dimensions in in.

a	b	c	G	J	Ø
12.20	12.20	5.51	10.24	3.74	0.43

Internal Wiring Diagram



Load Limits Curve



- (1) Nominal line supply + 10%
- (2) Nominal line supply
- (3) Nominal line supply - 10%