

Mobile Flat/Curved Panel Floor Stand - 60" - 100" TVs and Monitors, Heavy-Duty

MODEL NUMBER: DMCS60100XX



Mobile TV stand supports mounting of a large flat or curved panel television, monitor or interactive display/whiteboard.

Features

Bring the Presentation to Your AudienceThe DMCS60100XX combines a height-adjustable TV stand with the convenience of a rolling cart. Mount a flat or curved panel television, monitor or interactive whiteboard on this rolling TV cart and bring it to your audience in a classroom, lecture hall, office, conference room or other location where audio/video resources are shared. The DMCS60100XX accommodates most flat-panel displays from 60 to 100 inches, including Promethean whiteboards. It has an aluminum frame and supports up to 220 lb.

Effectively Share Audio/Video ResourcesAn alternative to purchasing multiple displays, the DMCS60100XX allows a large screen and its peripherals to be shared within a facility and stored in a secure area. This heavy-duty TV stand has four sturdy swivel casters that move smoothly through doorways and over thresholds. The casters lock to keep the stand in position while at rest. Each column has a handle to help you guide the cart's movement.

Easily Mount Your 60" to 100" Display and Adjust the Viewing AngleThe columns telescope in 2-inch increments, so you can adjust the height of the display mounting bracket from 47 to 65 inches above the floor. For hassle-free display compatibility, this rolling TV stand for flat-screen TVs supports the following VESA mounting hole patterns: 200 x 200, 300 x 300, 400 x 200, 400 x 400, 600 x 400, 800 x 400, 800 x 600 and 1000 x 600. The display angle can be adjusted from +5° to -10° for optimal viewing.

Conveniently Place Peripherals and Manage CablesThe upper shelf holds a webcam or small projector. The lower shelf holds a laptop or an audio/video component, such as a Blu-ray player. Add a clamp-on surge protector to the lower shelf to provide power protection for devices. The height of both shelves is adjustable. Cable management openings in the columns allow you to route power and connection cords, reducing clutter for a clean, professional look.

5-Year WarrantyThe DMCS60100XX is backed by a 5-year limited warranty, ensuring reliability and performance.

Highlights

- Holds most flat or curved panel displays from 60 to 100 in. and up to 220 lb.
- Accommodates interactive whiteboards, including Promethean models
- Display height adjusts from 47 to 65 in. for best viewing
- Locking swivel casters easily roll over carpet
- Shelves hold a webcam and a Blu-ray player or laptop

Applications

- View video in a multipurpose area where a permanent installation is not practical
- Move a display and webcam into a meeting room for web conferencing
- Create a temporary digital signage display in an auditorium
- Roll an interactive whiteboard between classrooms
- Easily move a flat-panel television for storage in a secure area

Package Includes

- All DMCS60100XX components (assembly required)
- Assembly fasteners
- Display mounting fasteners
- Hex key
- Wrench
- Owner's manual

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332224620
PHYSICAL	
Mounting Location	Floor
Shipping Dimensions (hwd / in.)	47.50 x 25.80 x 9.80
Shipping Dimensions (hwd / cm)	120.65 x 65.53 x 24.89
Shipping Weight (lbs.)	81.00
Shipping Weight (kg)	36.74
Unit Dimensions (hwd / in.)	46.02 x 44 x 27.6
Unit Weight (lbs.)	61
Unit Weight (kg)	27.67
Material of Construction	aluminum/steel
Color	Black; Silver
VESA Pattern (mm)	1000x600; 200x200; 300x300; 400x200; 400x400; 600x400; 800x400; 800x600
Motion	Tilt
Degrees of Motion	+5° to -10°
Maximum Weight Capacity (lbs.)	220
Maximum Weight Capacity (kg)	100
Minimum Screen Size (in.)	60
Maximum Screen Size (in.)	100
Minimum Screen Size (cm)	152.4
Maximum Screen Size (cm)	254
Number of Displays	1
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	Yes
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>