

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2043130010](#)
Status: **Active**
Overview: Coeur CST High-Current Interconnect System
Description: Coeur CST High-Current Female Socket, 8.00mm Diameter, with 1.00mm Float, Press-Fit

Documents:

[Drawing \(PDF\)](#) [Application Specification 2043130001-AS-000 \(PDF\)](#)
[Product Specification 2043130001-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	PCB Receptacles
Series	204313
Application	Power
Comments	Current and voltage performances are dependent upon application variables Embossed Tape & Reel and Tray packaging available. Contact Molex for information., Current and voltage performances are dependent upon application variables Embossed Tape & Reel and Tray packaging available. Contact Molex for information.
Datasheet Order No	987651-8619
Overview	Coeur CST High-Current Interconnect System
Product Name	Coeur CST
UPC	191128468671

Physical

Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	8.00mm
Durability (mating cycles max)	200
Glow-Wire Capable	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Net Weight	11.780/g
Number of Rows	1
Orientation	Vertical
PCB Retention	N/A
Packaging Type	Carton
Pitch - Mating Interface	N/A
Polarized to PCB	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Press-Fit


Electrical

Current - Maximum per Contact	200.0A
Voltage - Maximum	600V

Material Info

Reference - Drawing Numbers

Application Specification	2043130001-AS-000
Product Specification	2043130001-PS-000
Sales Drawing	2043130010-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[204313 Series](#)

Mates With

Coeur CST 8.00mm Pin [203263](#)

This document was generated on 06/21/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION