

ALANC10001



4.5 x 3.2 x 3.5 mm RoHS/RoHS II Compliant MSL = 1


Features

- Uniform transformer windings
- Fully automated production lines
- Meets IEEE 802.3u and 802.3ab standards
- Compatible with 10 BASE-T, 100 BASE-TX and 1000 BASE-T
- Symmetric Orientation
- Operating temperature range up to -40°C to +85°C
- RoHS Compliant
- 1CT:1CT Transformer

Applications

- Fast and gigabit Ethernet
- Servers, switches and routers
- IP cameras, surveillance, and phone
- Access points
- Industrial computers and robotics
- Networking and communications
- Broadcast video
- Set top box

Part Identification







ALANC10001



4.5 x 3.2 x 3.5 mm RoHS/RoHS II Compliant MSL = 1

Electrical Specifications at 25°C

Part Number	Insertion Loss (dB Max)	Return Loss (dB Min)				
	0.5-100 MHz	1-40 MHz	60 MHz	80 MHz	100 MHz	
ALANC10001-CDB3	1.5	18	16	12	10	

Part Number	Inductance (uH Min)	Leakage Inductance (uH)	Interwinding Capacitance (pF Max)	DC Resistance (Ω Max)		Hi Pot (Vrms)	Weight (g)		
Test Condition	@100kHz, 0.1V, 8mA DC Bias	@ 100KHz, 0.1V	@ 100KHz, 0.1V	CT to TD	TD+ to TD-	CT to MX	MX+ to MX-	6 sec.	Per Piece
ALANC10001-CDB3	200	0.5	35	2	3.5	2.5	5.0	1500	0.12






ALANC10001





4.5 x 3.2 x 3.5 mm RoHS/RoHS II Compliant MSL = 1

Mechanical Dimensions


C: 8-pin








RECOMMANDED LAND PATTERN





Unless otherwise specified, all tolerances are ± 0.25 in mm Dimensions: inch/ [mm]

BOTTOM VIEW





ALANC10001




4.5 x 3.2 x 3.5 mm RoHS/RoHS II Compliant MSL = 1


Schematics

8 - Pin

DB3



Reflow Profile



Zone	Description	Temperature	Time
1	Preheat / Soak	$T_{\text{SMIN}} \sim T_{\text{SMAX}}$ $150^{\circ}\text{C} \sim 200^{\circ}\text{C}$	60 ~ 180 sec.
2	Reflow	Т _ь 245°С	20 ~ 40 sec.
3	Peak heat	T _P 260°C±5°C	10 sec. MAX





ALANC10001





4.5 x 3.2 x 3.5 mm RoHS/RoHS II Compliant MSL = 1

Packaging

Tape and Reel: 2,200 pcs/reel Pieces Per Carton: 22,000 pcs Weight Per Carton: 4 kg (approx.)

Dimension of Carton: 345 x 345 x 290 mm





W	P	D	
12.0	8.0	Ө330	

Dimensions: mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 05-15-19

ABRACON IS ISO9001-2015 CERTIFIED