



## PDU15M2F8R Metered PDU

Engineered to distribute UPS, generator or utility AC power to multiple devices, servers and network/telecom equipment.

The CyberPower 10-outlet (2 Front and 8 Rear) rack mount metered power distribution unit (PDU15M2F8R) provides 120V 15A output. It distributes power to 10 NEMA 5-15R receptacles from a single NEMA 5-15P input, with unfiltered electrical pass-through. The current draw for connected equipment is displayed in amps on the front LCD for real-time load monitoring.

Designed for datacenters and other electrically demanding applications, this unit has a rugged, industrial-grade metal housing and a 15-foot AC power cord. It can be mounted either horizontally or vertically, includes a cord retention tray and is ETL/RoHS certified.

A Lifetime Warranty ensures that this PDU is free of defects in design, assembly, material and workmanship.

### Typical Applications

- Servers
- Network Devices
- Telecom Equipment

### Features

- Metered PDU
- Real-Time Load Monitoring
- Industrial-Grade Metal Housing
- Lifetime Warranty

# PDU15M2F8R Metered PDU

Engineered to distribute UPS, generator or utility AC power to multiple devices, servers and network/telecom equipment.

| GENERAL                      |  |
|------------------------------|--|
| Type                         | Metered PDU  |
| Phase                        | Single Phase   |
| INPUT                        |  |
| Voltage                      | 120V   |
| Current                      | 15A max  |
| Frequency                    | 50Hz/60Hz  |
| Plug Type                    | NEMA 5-15P   |
| Plug Style                   | Straight   |
| Cord Length                  | 15'  |
| OUTPUT                       |  |
| Nominal Output Voltage       | 120V   |
| Outlets - Total              | 10   |
| Outlet Type                  | NEMA 5-15R   |
| Outlets - Front              | 2  |
| Outlets - Rear               | 8  |
| Meter Readout                | Amperage   |
| Overload Protection          | 15A  |
| PHYSICAL                     |  |
| Rack Size                    | 1U   |
| Form Factors Supported       | 1U Rackmount, 0U Vertical Rackmount, Undercounter Installation Supported |
| Cord Retention Organizers    | Yes  |
| External Site Ground Pin     | Yes  |
| Adjustable Mounting Brackets | 2 sets (L-short, L-long)   |
| Dimensions (WxHxD) (in.)     | 17.5 x 1.75 x 2.25   |
| Weight (lbs.)                | 4.0  |
| ENVIRONMENTAL                |  |
| Operating Temperature        | 32°F to 95°F / 0°C to 35°C   |
| Operating Relative Humidity  | 0% - 95% non-condensing  |
| Storage Temperature          | 5°F to 113°F / -15°C to 45°C   |
| Maximum Operating Elevation  | 10,000 ft / 3,000 m  |
| Maximum Storage Elevation    | 50,000 ft / 15,000 m   |
| CERTIFICATIONS               |  |
| Safety                       | UL1363 certified by ETL (USA), CSA C22.2 (Canada)                        |
| Environmental                | RoHS Compliant   |
| WARRANTY                     |  |
| Product Warranty             | Lifetime   |