

MAX540H245S

- Waterproof and dustproof IP67 certified
- Mil Specs (STANAG 4280, DEF STAN 81-41)
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Holes for double padlocking
- Stackable interlocking system
- Thick body material
- Fully length hinges
- Nylon pins, corrosion free

Body and handle: polypropylene copolymer
Latches: nylon
Pins: nylon + 30% fiberglass
O-ring: polymer

COLOURS: black

EXTERNAL DIMENSIONS: 594 x 473 x H270 mm (23.39 x 18.62 x H10.63 inch)

INTERNAL DIMENSIONS: 538 x 405 x H245 mm (21.18 x 15.94 x H9.64 inch)

LID-BOTTOM DEPTH: 50 + 195 mm (1.97 + 7.68 inch)

WEIGHT WITH FOAM: 6.16 kg – 13.58 lbs

CARTON DIMENSIONS: 620 x 500 x 290mm – 24.40 x 19.68 x 11.41 inch

PCS PER CARTON: 1

WEIGHT OF THE FULL CARTON WITH FOAMS: 7.32 kg – 16.13 lbs.

MOULDING: injection molded

RANGE TEMPERATURE: -30 / 90°C (-22 / 194°F)

FEATURES: IP67, STANAG 4280, DEF STAN 81-41

CUSTOMIZATION: personalized nameplate/resin label

ACCESSORIES: cubed foams, padded dividers, lid organizer

