

## MAX505STR

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Holes for double padlocking
- Holes for shoulder strap
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins, corrosion free

Body and handle: polypropylene copolymer

Latches: nylon

Pins: nylon + 30% fiberglass

O-ring: polymer

COLOURS: Black, orange, sahara

EXTERNAL DIMENSIONS: 555 x 428 x H258 mm (21.85 x 16.85 x H10.16 inch)

INTERNAL DIMENSIONS: 500 x 350 x H194 mm (19.69 x 13.78 x H7.64 inch)

LID-BOTTOM DEPTH: 58 + 136 mm (2.28 + 5.36 inch)

WEIGHT WITH FOAM: 5.540 kg – 12.21 lbs

CARTON DIMENSIONS: 580 x 270 x 470 mm ( 22.82 x 10.63 x 18.50 inch)

PCS PER CARTON: 1

WEIGHT OF THE FULL CARTON WITH FOAMS: 6.64 Kg – 14.63 lbs

CAPACITY: 25kg – 55 lbs.

MOULDING: injection molded

RANGE TEMPERATURE: -30 / 90°C (-22 / 194°F)

FEATURES: wheels, extendable handle

CUSTOMIZATION: personalized nameplate/resin label

ACCESSORIES: cubed foams, lid organizer, padded dividers, padded shoulder strap

