


NOTE:

1. CABLE:
2. LENGTH:L.
3. CONNECTORS: MICRO USB(B)F 5P ,TYPE C M*1PCS(SHELL NICKEL).
4. MOLD: MOLDING TYPE.
5. CONTACTS:
6. Test machine test condition.
A.100% OPEN,SHORT&INTERMITANCE TEST.
B.CONDUCTOR RESISTANCE:3ohms MAX:
C.INSULATION RESISTANCE:10MΩ Min/,10ms:
7. ALL MUST BE MEET ON ROHS COMPLIANT.



1PCS/OPP BAG+LABEL

COMPANY	CDL		ITEM NO.	PSG91705	NO	B
REVISION	DATE	DISCRIPTION	DRAWN BY			
REV.A/0	2019.06.25		DESIGNED BY			
			APPROVAL BY			

SCALE	NON
UNIT(mm)	
DRAWING NO.	