

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0787261004](#)
Status: **Active**
Overview: DDR4 DIMM Sockets
Description: DDR4 DIMM Socket, Vertical Through-Hole, 0.76µm Gold Plating, 288 Circuits, PCB Thickness 1.57mm, Tail Length 2.67mm, Black Housing, White Latch

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-78726-001-000 \(PDF\)](#)
[Product Specification PS-78726-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-78726-002-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Memory Module Sockets
 Series [78726](#)
 Component Type Socket
 Electrical Model Yes
 JEDEC Outline MO-309
 Overview [DDR4 DIMM Sockets](#)
 Product Name DDR4 DIMM
 UPC 887191398853

Physical


Circuits (Loaded) 288
 Circuits (maximum) 288
 Durability (mating cycles max) 25
 Entry Angle Vertical (Top Entry)
 Flammability 94V-0
 Housing Color Black
 Keying to Mating Part Yes
 Latch Color White
 Material - Metal Copper Alloy
 Material - Plating Mating Gold over Nickel
 Material - Plating Termination Tin over Nickel
 Material - Resin Nylon
 Net Weight 6.626/g
 PC Tail Length 2.67mm
 PCB Locator Yes
 PCB Retention Yes
 PCB Thickness - Recommended 1.57mm
 Packaging Type Tray
 Pitch - Mating Interface 0.85mm
 Pitch - Termination Interface 0.85mm
 Plating min - Mating 0.762µm
 Plating min - Termination 2.540µm
 Temperature Range - Operating -55° to +85°C
 Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 0.75A
 Voltage - Maximum 29V AC (RMS)/DC

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
 Lead-freeProcess Capability SMC&WAVE



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/88/2018 (15
 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[78726 Series](#)

Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Application Specification	AS-78726-002-001
Electrical Model Document	787260005-000, 787260021REVA-000, 787260022REVA-000, EE-78726-002, EE-78726-004
Packaging Specification	PK-78726-001-000
Product Specification	PS-78726-001-001
S-Parameter Model	SP-78726-002, SP-78726-004
Sales Drawing	SD-78726-002-000

This document was generated on 06/04/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION