


NOTE:

1. CABLE: UL2725,AL+B-FOIL,32AWG*1P+24AWG*2C+F+(32AWG*1P+D+AL+MYLAR)*2C, WHITE COLOR,OD=5.0±0.2mm,PVC JACKET.
2. LENGTH: 0.395M.
3. CONNECTORS: ∅3.5 STEREO JACK*2PCS,TYPE C M*1PCS, USB3.0AF*3PCS(BLUE INSULATION)(SHELL NICKEL).
4. MOLD: MOLDING TYPE.
5. CONTACTS:
6. Test machine test condition.
 A.100% OPEN,SHORT&INTERMITANCE TEST.
 B.CONDUCTOR RESISTANCE: 3ohms MAX:
 C.INSULATION RESISTANCE: 10MΩ Min/,10ms:
7. ALL MUST BE MEET ON ROHS COMPLIANT.



1PCS/OPP BAG+LABEL

COMPANY	CDL		ITEM NO.	PSG91711	NO	B	PRO-SIGNAL	SCALE	NON
REVISION	DATE	DISCRIPTION	DRAWN BY					UNIT(mm)	
REV.A/0	2019.06.25		DESIGNED BY					DRAWING NO.	
			APPROVAL BY						