

Description:

This is a silicon PNP transistor in a TO-39 type case designed primarily for amplifier and switching applications. This device features high breakdown voltage, low leakage current, low capacity, and beta useful over an extremely wide current range.

Maximum Ratings:

Characteristic	Symbol	Rating	Unit
Collector - Base Voltage	V_{CBO}	40	V
Collector - Emitter Voltage	V_{CEO}		
Emitter - Base Voltage	V_{EBO}	7	
Continuous Collector Current	I_C	1	A
Total Device Dissipation ($T_A = +25^\circ\text{C}$), Derate above 25°C	P_D	1	W
Total Device Dissipation ($T_C = +25^\circ\text{C}$), Derate above 25°C		5.7	
		6	mW/ $^\circ\text{C}$
		34	
Operating Junction Temperature,	T_J	-65 to +200	$^\circ\text{C}$
Storage Temperature Range,	T_{stg}	-65 to +200	
Thermal Resistance, Junction-to-Case,	R_{thJC}	29	$^\circ\text{C}/\text{W}$
Lead Temperature (During Soldering, 1/16" from case, 60 sec max)	T_L	300	$^\circ\text{C}$

Electrical Characteristics: ($T_A = +25^\circ\text{C}$ Unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
-----------	--------	-----------------	-----	-----	-----	------

OFF Characteristics

Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = 100\text{mA}, I_B = 0$	40	-	-	V
Collector Cut-Off Current	I_{CBO}	$V_{CB} = 40\text{V}, I_E = 0$	-	-	100	μA
Emitter Cut-Off Voltage	I_{EBO}	$V_{BE} = 7\text{V}, I_C = 0$			500	

ON Characteristics (Note 1)


DC Current Gain	h_{FE}	$V_{CE} = 1\text{V}, I_C = 100\text{mA}$	40	-	-	-
		$V_{CE} = 1\text{V}, I_C = 250\text{mA}$	30		150	
		$V_{CE} = 1\text{V}, I_C = 500\text{mA}$	20		-	
		$V_{CE} = 1\text{V}, I_C = 1\text{A}$	10		-	
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = 1\text{A}, I_B = 125\text{mA}$	-	-	0.6	V
Base-Emitter On Voltage	$V_{BE(sat)}$	$I_C = 1\text{A}, I_B = 100\text{mA}$			1.5	

Small-Signal Characteristics

Small-Signal Current Gain	h_{fe}	$V_{CE} = 10\text{V}, I_C = 50\text{mA}, f = 1\text{KHz}$	25	-	-	-
Output Capacitance	C_{cbo}	$V_{CB} = 10\text{V}, f = 0.1\text{MHz}$	-	-	100	pF
Input Capacitance	C_{ibo}	$V_{BE} = 500\text{mV}, f = 1\text{MHz}$			110	pF

Note:

1. Pulse Test : Pulse Width $\leq 300\mu\text{s}$, Duty Cycle $\leq 1\%$



Dimensions	A	B	C	D	E	F	G	H	I	J	K
Min.	8.5	7.74	6.09	0.4	-	2.41	4.82	0.71	0.73	12.7	42°
Max.	9.39	8.5	6.6	0.53	0.88	2.66	5.33	0.86	1.02	-	48°

Dimensions : Millimetres

Pin Configuration:

1. Emitter
2. Base
3. Collector

Part Number Table

Description	Part Number
Transistor, PNP, 3A, 40V, TO39	2N4234

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.