

multicomp PRO



Features:

- For High-Speed Switching Applications
- Common Anode



Applications:

High speed switching application

SOT-23

Max. Rating @ T_A = 25°C unless otherwise specified

Parameter	Symbol	Limits	Unit
Non-repetitive peak reverse voltage	Vrm	100	V
Peak repetitive reverse voltage Working peak reverse voltage DC reverse voltage	Vrrm Vrms Vr	75	V
Forward continuous current	lF	300	mA
Non-repetitive forward surge current @t = 1ms @t = 1s	Ігѕм	2 1	A
Power dissipation	PD	350	mW
Thermal resistance junction to ambient air	R _{θJA}	357	°C/W
Operating junction temperature range	Тј	150	°C
Storage temperature range	Тѕтс	-65 to +150	°C


Electrical Characteristics @ T_A = 25°C unless otherwise specified

Parameter	Symbol	Conditions	Min.	Max.	Unit
Reverse breakdown voltage	V(br)r	Ι κ = 2.5μΑ	75	-	V
Forward voltage	VF	IF = 1mA IF = 10mA IF = 50mA IF = 150mA	-	715 855 1,000 1,250	V
Reverse leakage current	lĸ	V _R = 75V V _R = 20V	-	2.5 25	μA nA
Diode capacitance	Ср	Vr =0V, f=1MHz	-	2	pF
Reverse recovery time	trr	IF = IR = 10mA, Irr = 0.1 × IR, RL = 100Ω	-	4	ns

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




Typical Characteristics @ TA = 25°C unless otherwise specified



Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




Plastic surface mounted package



SOT-23				
Dim	Min	Max		
А	2.85	2.95		
В	1.25	1.35		
С	1 Typical			
D	0.37	0.43		
E	0.35	0.48		
G	1.85	1.95		
Н	0.02	0.1		
J	0.1Typical			
К	2.35	2.45		
All Dimensions in mm				

Soldering Footprint



Package Information

Device	Package	Shipping
BAW56-7-F	SOT-23	3,000 / Tape & Reel

Part Number Table

Description	Part Number	
Surface mount switching diode	BAW56-7-F	

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

