

Ceramic Disc Capacitor

multicomp PRO


**RoHS
Compliant**



Specifications:

Capacitance	: 22pF, tolerance : 5%
Working Voltage	: 1kV DC Q 840 minimum
D.F.	: Maximum
I.R.	: 10,000MΩ minimum at 500 V dc, 60 s
Test Voltage	: 2kV DC 1-5 s
Operating Temperature Range	: -25°C to +85°C
Capacitance and DF / Q are measured at 1kHz ±0.2kHz 50m Vrms 25°C	

Diagram



Dimensions : Millimetres

Dimensions

D : 6mm maximum
T : 4mm maximum
L : 25.4mm minimum
F : 6.34 ±1mm
P : 3mm maximum
d : 0.6 ±0.05mm
H : 9mm maximum

Part Number Table

Description	Part Number
Ceramic Disc Capacitor	MCC1C220J3AS6L-RH

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO