Neon Lamp






Feature:

· Neon lamp without series resistor

Specifications:

Lamp Base Type : Wire Ended
Bulb Size : 6mm / T-2
Lead Length : 30mm



Part Number Table

Description	Maximum Strike Voltage		Nominal Current	Recommended Series Resistor		Brightness	Lead	Wire Ended	Part Number
	AC	DC	(mA)	110V AC	240V AC		Length	Types	
Neon Lamp, Wire Ended, T2	65	90	0.55	100K 1/4W	330K 1/4W	Standard	30	6mm, T2	MC08320000
	95	135	4.5	12K 1/4W	39K 1/4W	High			MC08310015

Dimensions: Millimetres

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

