

Transistor, NPN TO-3

multicompPRO



Description:

High-power industrial transistor

NPN silicon power transistor designed for applications in industrial and commercial equipment including high fidelity audio amplifiers, series and shunt regulators and power switches

Features:

- The 2N3442 is a Silicon power base transistor for high power audio, series pass power supplies, disk-head positioners and other linear application. These devices can also be used in power switching circuits such as converters or inverters
- Higher safe operating area than 2N3442 at $V_{CE} > 40V$
- Low saturation voltages
- High power dissipation capability

Maximum Ratings

Rating	Symbol	Value	Unit
Collector-Emitter Voltage	V_{CEO}	140	V DC
Collector-Base Voltage	V_{CB}	160	
Emitter-Base Voltage	V_{EB}	7	
Collector Current-Continuous -Peak	I_C	10 15	A DC
Base Current-Continuous -Peak	I_B	7 -	
Total Power Dissipation at $T_C = 25^\circ C$ Derate above $25^\circ C$ (Note 2)	P_D	117 0.67	W W/ $^\circ C$
Operating and Storage Junction Temperature Range	T_J, T_{STG}	-65 to +200	$^\circ C$

Thermal Characteristics

Characteristic	Symbol	Max.	Unit
Thermal Resistance Junction to Case	$R_{\theta jc}$	1.17	$^\circ C/W$

Max. ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

1. Indicates JEDEC registered data.
2. This data guaranteed in addition to JEDEC registered data.

Transistor, NPN

T0-3

multicompPRO


Electrical Characteristics (TC = 25°C unless otherwise noted)

Characteristic	Symbol	Min.	Max.	Unit
Off Characteristics				
Collector-Emitter Sustaining Voltage ($I_C = 200\text{mA DC}$, $I_B = 0$)	$V_{EO(sus)}$	140	-	V DC
Collector Cut off Current ($V_{CE} = 140\text{V DC}$, $I_B = 0$)	I_{CEO}	-	200	mA DC
Collector Cut off Current ($V_{CE} = 140\text{ V DC}$, $V_{BE(off)} = 1.5\text{ V DC}$) ($V_{CE} = 140\text{V DC}$, $V_{BE(off)} = 1.5\text{V DC}$, $T_C = 150^{\circ}\text{C}$)	I_{CEX}	-	5 30	
Emitter Cut off Current ($V_{EB} = 7\text{V DC}$ $I_C = 0$)	I_{EBO}	-	5	
On Characteristic (Note 3)				
DC Current Gain ($I_C = 3\text{A DC}$, $V_{CE} = 4\text{V DC}$) ($I_C = 10\text{A DC}$, $V_{CE} = 4\text{V DC}$)	h_{FE}	2 7.5	70 -	-
Collector-Emitter Saturation Voltage ($I_C = 10\text{A DC}$, $I_B = 2\text{A DC}$)	$V_{CE(sat)}$	-	5	V DC
Base-Emitter On Voltage ($I_C = 10\text{A DC}$, $V_{CE} = 4\text{V DC}$)	$V_{BE(on)}$	-	5.7	
Dynamic Characteristics				
Current-Gain - Bandwidth Product (Note 4) ($I_C = 2\text{A DC}$, $V_{CE} = 4\text{V DC}$, $f_{test} = 40\text{kHz}$)	f_T	80	-	kHz
Small-Signal Current Gain ($I_C = 2\text{A DC}$, $V_{CE} = 4\text{V DC}$, $f = 1\text{kHz}$)	h_{fe}	12	72	-

Note:

(3) Pulse Test : Pulse Width = 300μs, Duty Cycle ≤2%


(4) $f_T = |h_{fe}| \cdot f_{test}$



Transistor, NPN TO-3

multicompPRO


Active-Region Safe Operating Area Information




There are two limitation on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate I_C - V_{CE} limits of the transistor that must be observed for reliable operation i.e., the transistor must not be subjected to greater dissipation than curves indicate.

The data is based on $T_{J(PK)} = 200^\circ\text{C}$; T_C is variable depending on conditions. At high case temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown.

DC Current Gain



Collector-Saturation Region




multicompPRO

Transistor, NPN

TO-3

Dimensions:



Dimensions	Min.	Max.
A	1.55 (39.37)	Reference
B	-	1.05 (26.67)
C	0.25 (6.35)	0.335 (8.51)
D	0.038 (0.97)	0.043 (1.09)
E	0.055 (1.4)	0.07 (1.77)
G	0.43 (10.92)	BSC
H	0.215 (5.46)	BSC
K	0.44 (11.18)	0.48 (12.19)
L	0.665 (16.89)	BSC
N	-	0.83 (21.08)
Q	0.151 (3.84)	0.165 (4.19)
U	1.187 (30.15)	BSC
V	0.131 (3.33)	0.188 (4.77)

Dimensions : Inches (Millimetres)

Pin Configuration:

- Pin 1. Base
2. Emitter
Collector (Case)

Part Number Table

Description	Part Number
Transistor, NPN, TO-3	2N3442

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.