

Mountz FG Precision Preset Torque Screwdriver

THE MOST ADVANCED HAND DRIVER IN THE WORLD

- Unmatched quality you can count on
- Calibration life 4x ISO standards
- Two year unlimited warranty
- Lifetime warranty against manufacturer defects
- Accuracy and precision delivered for all fastening applications







50 years of innovation in the palm of your hand

THE STATE-OF-THE-ART PRECISION TORQUE DRIVER.

Engineered and assembled in Silicon Valley, the Mountz FG line of precision preset torque screwdrivers are the most advanced hand tools in the world.

Preset hand torque screwdrivers are ideal for fastening applications where operators repeatedly assemble parts at the same torque setting. These cam-over drivers include a highly sophisticated locking mechanism, a sleek and ergonomic design, and a low-impact reset mechanism to deliver the highest level of performance and comfort available.

Precision and accuracy delivered every time

BREAKTHROUGH ACCURACY AND REPEATABILITY INCREASES OPERATOR CONFIDENCE AND OVERALL QUALITY OF ASSEMBLY.

Mountz FG tools stay in calibration 4X longer than the most stringent industry standard (ISO 6789). Engineered with a cam-over mechanism, the poka-yoke screwdriver prevents over torque. You can give Mountz FG tools to any

operator and have the confidence that they will deliver the correct torque, time

after time.

Our unique bearing system eliminates axial (end) and side loads by the operator, increasing consistency of torque delivered and joint reliability.





Torque tools that turn heads

INNOVATIVE AND ERGONOMIC, YES. SLEEK AND BEAUTIFUL, ABSOLUTELY!

Innovative, ergonomic, sleek, stunning. In this revolutionary new precision torque tool line, Mountz has integrated industry-changing design improvements that boost accuracy, increase productivity, and dramatically expand longevity. These tools define performance. And, they are sleek and great feeling tools! So you better get used to hearing workers say, "Hand me the Mountz."



The last precision torque screwdriver you'll ever need to buy!

We've tested them over two million cycles in our controlled lab environment and we still can't break them!

It's why we have an industry-leading warranty.

- Mountz FG tools are the only cam-over drivers on the market to offer a two year unlimited warranty. If it breaks in any way, we'll fix it or replace it for free.
- Lifetime guarantee against manufacturing defects. We only make the highest quality products. This driver will not have a defect, we stake our quality reputation on it.
- Warranty includes a free first calibration within the first year (if needed).

FEATURES AND BENEFITS

- A complete redesign and significant upgrade of existing solutions
- Engineered in the Silicon Valley and designed for improved performance, longevity, and productivity.
- Exceeds the strictest ISO quality standards many times over
- Advanced cam-over technology provides a completely smooth reset reducing the risk of users loosening fasteners or breakage
- Patented secure bit locking mechanism with one-touch release can only be activated by the user for greater flexibility of applications and efficiency on the line

- Reduced bit wear lowers the incidence of bits falling out, which can slow production or cause product damage
- Unmatched security of the tamper-proof internal adjustment. No external adjustment scale—must be preset using a torque analyzer.
- Unique bearing system eliminates axial load and side load on the fastener applied by the operator.
- New design improves serviceability, reduces downtime, and enables replacement of individual parts to extend the life of your investment.

- Ergonomic handles are designed with fewer flutes and larger recesses to make the tools easier to hold, less likely to cause hand fatigue, and makes drivers easier to clean.
- Enable quick and errorfree tool and torque setting identification with color-coding labels
- All models provide bi-directional operation and are calibrated in either the CW or CCW direction.
- Designed and manufactured to meet or exceed the accuracy and repeatability requirements of ISO 6789: 2017 (+/- 6% of setting).




MOUNTZ FG PRESET PRECISION HAND SCREWDRIVER LINEUP

MODEL	ITEM NO.	TORQUE RANGES		DDW/E 0175	LABEL		
		AMERICAN	S.I.	DRIVE SIZE	COLOR	WEIGHT	LENGTH
FG-8i	076546	0.8-8 lbf.in	9-90 cN.m	1/4" F/Hex	Blue	7.3 oz.	5.2"
FG-8i	076551	0.8-8 lbf.in	9-90 cN.m	1/4" F/Hex	Red	7.3 oz.	5.2"
FG-8i	076556	0.8-8 lbf.in	9-90 cN.m	1/4" F/Hex	Green	7.3 oz.	5.2"
FG-8i	076561	0.8-8 lbf.in	9-90 cN.m	1/4" F/Hex	Gold	7.3 oz.	5.2"
FG-20i	076547	2-20 lbf.in	22-226 cN.m	1/4" F/Hex	Blue	7.3 oz.	5.2"
FG-20i	076552	2-20 lbf.in	22-226 cN.m	1/4" F/Hex	Red	7.3 oz.	5.2"
FG-20i	076557	2-20 lbf.in	22-226 cN.m	1/4" F/Hex	Green	7.3 oz.	5.2"
FG-20i	076562	2-20 lbf.in	22-226 cN.m	1/4" F/Hex	Gold	7.3 oz.	5.2"
FG-40i*	076548	4-40 lbf.in	0.4-4.5 N.m	1/4" F/Hex	Blue	11.5 oz.	6.3"
FG-40i*	076553	4-40 lbf.in	0.4-4.5 N.m	1/4" F/Hex	Red	11.5 oz.	6.3"
FG-40i*	076558	4-40 lbf.in	0.4-4.5 N.m	1/4" F/Hex	Green	11.5 oz.	6.3"
FG-40i*	076563	4-40 lbf.in	0.4-4.5 N.m	1/4" F/Hex	Gold	11.5 oz.	6.3"
FG-125i*	076549	25-125 lbf.in	2.8-14.1 N.m	1/4" F/Hex	Blue	11.5 oz.	6.3"
FG-125i*	076554	25-125 lbf.in	2.8-14.1 N.m	1/4" F/Hex	Red	11.5 oz.	6.3"
FG-125i*	076559	25-125 lbf.in	2.8-14.1 N.m	1/4" F/Hex	Green	11.5 oz.	6.3"
FG-125i*	076564	25-125 lbf.in	2.8-14.1 N.m	1/4" F/Hex	Gold	11.5 oz.	6.3"



*A removable, sliding T-bar is supplied with FG-40i and FG-125i models.

Note: IFR (Impact Free Resetting) and OWC (One-Way Clutch with Locking Mechanism) screwdriver models are available.







mountztorque.com

ABOUT MOUNTZ

mountz, The Torque Tool Specialists*, has been a leader in the torque tool industry for more than 50 years. Engineered in the Silicon Valley and serving the globe, Mountz focuses on delivering high-quality torque products, services, and solutions to ensure customers can always proceed with confidence. We are committed to forging a safer world through precision and accuracy, and by innovating every day.

SILICON VALLEY HEADQUARTERS AND SERVICE CENTER

1080 N. 11th St., San Jose, CA 95112 408-292-2214 / M-F 6am-5pm PST

ALABAMA DISTRIBUTION AND SERVICE CENTER

19051 Underwood Road, Foley, AL 36535