Surface Mount Fast Recovery Glass Passivated Rectifier

multicomp PRO



Features:

- Fast switching for high efficiency
- Low cost
- Diffused junction
- Low reverse leakage current
- Low forward voltage drop
- High current capability
- The plastic material carries UL recognition 94V-0

Mechanical Data:

Molded Plastic
Indicated by cathode band
0.002 ounces, 0.053 grams
Any
800 Volts
1 Ampere

Maximum Ratings and Electrical Characteristics:

Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

Characteristics	Symbol	Values	Unit
Max. Recurrent Peak Reverse Voltage	Vrrm	800	
Max. RMS Voltage	Vrms	560	V
Max. DC Blocking Voltage	VDC	800	
Max. Average Forward Rectified Current @T A=75°C	l(AV)	1	
Peak Forward Surge Current 8.3ms Single Half Sine-Wave Super Imposed on Rated Load (JEDEC Method)	IFSM	30	A
Peak Forward Voltage at 1A DC	Vf	1.3	V
Max. DC Reverse Current at $T_A = 25^{\circ}C$ Rated DC Blocking Voltage at $T_A = 125^{\circ}C$	lr	5 100	μA
Maximum Reverse Recovery Time (Note 1)	Trr	500	nS
Typical Junction Capacitance (Note 2)	Сл	15	рF
Typical Thermal Resistance (Note 3)	Reja	25	°C/W
Operating Temperature Range	TJ	-55 to +150	°C
Storage Temperature Range	Tstg	-55 to +150	°C

Notes:

1. Measured with IF = 0.5A, IR = 1A, IRR = 0.25A

2. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.


- 3. Thermal resistance junction to ambient.
- 4. The typical data above is for reference only


Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



multicomp PRO

Ratings and Characteristic Curves





NUMBER OF CYCLES AT 60Hz





FIG.4-TYPICAL FORWARD CHARACTERISTICS




INSTANTANEOUS FORWARD VOLTAGE, VOLTS

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

multicomp PRO

Surface Mount Fast Recovery Glass Passivated Rectifier

multicomp PRO



Dimensions : Inches (Millimetres)

Part Number Table

Description	Part Number
Surface Mount Fast Recovery Glass Passivated Rectifiers, 1A 800V SMA	RS1K+

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

