Glass Passivated Bridge Rectifier





Features

- Rating 600V PRV
- · Ideal for printed circuit board
- · Low forward voltage drop, high current capability
- Reliable low cost construction utilizing molded plastic technique results in inexpensive product
- · The plastic material has U/L flammability classification 94V-0

Maximum Ratings And Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%

Characteristic	Symbol	Values	Unit
Maximum Recurrent Peak Reverse Voltage	Vrrm	600	V
Maximum RMS Voltage	VRMS	420	
Maximum DC Blocking Voltage	VDC	600	
Maximum Average Forward (with heatsink Note 2) Rectified Current @ Tc = 100°C (without heatsink)	I(AV)	8 2.9	А
Peak Forward Surge Current 8.3ms Single Half Sine-Wave Super Imposed on Rated Load (JEDEC Method)	Ігѕм	200	
Typical Forward Voltage at 4A DC	VF	0.89	V
Maximum Forward Voltage at 4A DC		0.9	
Maximum DC Reverse Current @ T _J = 25°C at Rated DC Blocking Voltage @ T _J = 125°C	lR	10 120	μA
I ² t Rating for Fusing (t<8.3ms)	l²t	166	A ² s
Typical Junction Capacitance Per Element (Note1)	Сл	55	pF
Typical Thermal Resistance	Rejc	1.8	°C/W
Operating Temperature Range	TJ	-55 to +150	°C
Storage Temperature Range	Тѕтс		

Notes:

- 1. Measured at 1MHz and applied reverse voltage of 4V DC
- 2. Device mounted on 75mm × 75mm × 1.6mm Cu plate heatsink.
- 3. The typical data above is for reference only


Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro





Glass Passivated Bridge Rectifier





Rating and Characteristic Curves












Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Glass Passivated Bridge Rectifier



Dimension:



Dimensions: Inches (Millimetres)

Part Number Table

Description	Part Number	
Glass Passivated Bridge Rectifier	4GBJ806U	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

