

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNK Series

## General Information

<b>Extended Product Type:</b>	ZK4-PE-4P
<b>Product ID:</b>	1SNK706152R0000
<b>EAN:</b>	3472597061523
<b>Catalog Description:</b>	ZK4-PE-4P PI-Spring clamp Terminal Block - Ground - Green Yellow
<b>Long Description:</b>	Improve the safety of your installation in the event of a short-circuit thanks to our screwless rail contact: - Rail contact non operator dependent, - Performances above the requirements of the IEC 60947-7-2 terminal block standard, - Secured snap on or off the rail, - Profile aligned with ZK4-4P.

## Ordering

<b>Color:</b>	Green-Yellow
<b>Minimum Order Quantity:</b>	20 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNK162028D0201
<b>Instructions and Manuals:</b>	1SNK160027C0201

## Dimensions

<b>Product Net Width:</b>	6 mm
<b>Product Net Height:</b>	96.2 mm
<b>Product Net Length:</b>	41.2 mm
<b>Product Net Depth / Length:</b>	41.2 mm
<b>Product Net Weight:</b>	18.4 g

## Technical

<b>Rated Cross-Section:</b>	4 mm <sup>2</sup>
<b>Spacing:</b>	6 mm
<b>Connection Type:</b>	PI Spring
<b>Function:</b>	Ground
<b>Number of Levels:</b>	1
<b>Connecting Capacity Main Circuit:</b>	Spring Clamp / Flexible 1x 0.5 ... 4 mm <sup>2</sup> Spring Clamp / Rigid 1x 0.5 ... 6 mm <sup>2</sup> Spring Clamp / With Insulated Ferrule 1x 0.5 ... 4 mm <sup>2</sup> Spring Clamp / Without Insulated Ferrule 1x 0.5 ... 4 mm <sup>2</sup>
<b>Gauge Type:</b>	2.9 mm Dia.

<b>Rated Short-time Withstand Current (<math>I_{cw}</math>):</b>	for 1 s 480 A
<b>Rated Impulse Withstand Voltage (<math>U_{imp}</math>):</b>	8000 V
<b>Dielectric Test Voltage:</b>	2200 V
<b>Pollution Degree:</b>	3
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Wire Stripping Length:</b>	12.5 mm

## Technical UL/CSA

<b>Connecting Capacity Main Circuit UL/CSA:</b>	Spring Clamp / Rigid 1x 26 ... 10 AWG Spring Clamp / With Insulated Ferrule 1x 26 ... 12 AWG Spring Clamp / Without Insulated Ferrule 1x 26 ... 12 AWG
<b>Connecting Capacity UL/CSA:</b>	Stranded 10 AWG
<b>Flammability According to UL94:</b>	V0

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>Resistance to Vibrations acc. to IEC 60068-2-6:</b>	Compliant
<b>RoHS Status:</b>	Following EU Directive 2011/65/EU

## Certificates and Declarations (Document Number)

<b>ATEX Certificate:</b>	1SND162009A1702
<b>BV Certificate:</b>	1SND162013A0203
<b>CB Certificate:</b>	1SND162017A0200
<b>CSA Certificate:</b>	1SND162014A0206
<b>cUL Certificate:</b>	1SND162012A0204
<b>Declaration of Conformity - CE:</b>	1SND225112U1004
<b>DNV Certificate:</b>	1SND162023A0200
<b>EAC Certificate:</b>	1SND161010A1100
<b>Environmental Information:</b>	1SND220072E1002
<b>Instructions and Manuals:</b>	1SNK160027C0201
<b>RoHS Information:</b>	1SND230535F0201

## Classifications

<b>Object Classification Code:</b>	X
------------------------------------	---

**ETIM 4:** EC000901 - Ground terminal block

---

**ETIM 5:** EC000901 - Ground terminal block

---

**ETIM 6:** EC000901 - Ground terminal block

## Container Information

**Package Level 1 Units:** 20 piece

---

**Package Level 1 Width:** 101 mm

---

**Package Level 1 Depth / Length:** 120 mm

---

**Package Level 1 Height:** 50 mm

---

**Package Level 1 Gross Weight:** 0.388 kg

---

**Package Level 1 EAN:** 3472597061523

---

**Package Level 2 Units:** 360 piece

---

**Package Level 2 Width:** 300 mm

---

**Package Level 2 Depth / Length:** 400 mm

---

**Package Level 2 Height:** 200 mm

---

**Package Level 2 Gross Weight:** 6.984 kg

---

**Package Level 3 Units:** 17280 piece

---

**Product Packing Type:** Box

