

### **Features**


- Superior circuit protection
- Overcurrent protection
- Blocks surges up to rated voltage limit
- High-speed performance
- Small SMT package
- RoHS compliant\*

# **TBU-DF Series - TBU® High-Speed Protectors**

### **General Information**

The TBU-DF Series of Bourns® TBU® products are low capacitance dual bidirectional high-speed Electronic Current Limiters (ECLs), constructed using MOSFET semiconductor technology, and designed to protect against faults caused by short circuits, overvoltage transients and faults in battery cells, up to rated limits.

The TBU® high-speed protector placed in the system circuit will monitor the current with the MOSFET detection circuit triggering to provide an effective barrier behind which sensitive electronics will not be exposed to large voltages or currents during transient events.



The TBU® device is provided in a surface mount DFN package and meets industry standard requirements such as RoHS and Pb Free solder reflow profiles.

### Absolute Maximum Ratings (@ T<sub>A</sub> = 25 °C Unless Otherwise Noted)

Symbol	Parameter	Part Number	Value	Unit
V.	Peak impulse voltage withstand with duration less than 10 ms	TBU-DF055-xxx-WH	550	V
V <sub>imp</sub>	reak impulse voltage withstand with duration less than 10 ms	TBU-DF085-xxx-WH	850	V
V	Continuous A.C. BMS voltage	TBU-DF055-xxx-WH	250	V
V <sub>rms</sub>	Continuous A.C. RMS voltage	TBU-DF085-xxx-WH	425	V
T <sub>op</sub>	Operating temperature range	-55 to +125	°C	
T <sub>stg</sub>	Storage temperature range	-65 to +150	°C	
T <sub>amax</sub>	Maximum Ambient Temperature	+125	°C	

### Electrical Characteristics (@ T<sub>A</sub> = 25 °C Unless Otherwise Noted)

Symbol	Parameter	Part Number	Min.	Тур.	Max.	Unit	
I <sub>trigger</sub>	Current required for the protected state	e device to go from operating state to	TBU-DFxxx-050-WH TBU-DFxxx-100-WH TBU-DFxxx-200-WH TBU-DFxxx-300-WH TBU-DFxxx-500-WH	50 100 200 300 500	75 150 300 450 750	100 200 400 600 1000	mA
R <sub>device</sub>	Series resistance of the TBU® device	V <sub>imp</sub> = 550 V I <sub>trigger</sub> (min.) = 50 mA V <sub>imp</sub> = 550 V I <sub>trigger</sub> (min.) = 100 mA V <sub>imp</sub> = 550 V I <sub>trigger</sub> (min.) = 200 mA V <sub>imp</sub> = 550 V I <sub>trigger</sub> (min.) = 300 mA V <sub>imp</sub> = 550 V I <sub>trigger</sub> (min.) = 500 mA V <sub>imp</sub> = 850 V I <sub>trigger</sub> (min.) = 50 mA V <sub>imp</sub> = 850 V I <sub>trigger</sub> (min.) = 100 mA V <sub>imp</sub> = 850 V I <sub>trigger</sub> (min.) = 200 mA V <sub>imp</sub> = 850 V I <sub>trigger</sub> (min.) = 300 mA V <sub>imp</sub> = 850 V I <sub>trigger</sub> (min.) = 300 mA V <sub>imp</sub> = 850 V I <sub>trigger</sub> (min.) = 500 mA	TBU-DF055-050-WH TBU-DF055-100-WH TBU-DF055-200-WH TBU-DF055-300-WH TBU-DF055-500-WH TBU-DF085-050-WH TBU-DF085-100-WH TBU-DF085-200-WH TBU-DF085-300-WH	12 9.5 7.5 6 5 23 14.5 12.5 15	730	26 18.5 15.5 14 13 38 26.5 22.5 26 25	Ω
R <sub>match</sub>	Package resistance m			+0.5	Ω		
t <sub>block</sub>	Time for the device to		1		μs		
lQ	Current through the tri		0.5		mA		
V <sub>reset</sub>	Voltage below which the triggered TBU® device will transition to normal operating state				16	20	V
R <sub>th(j-a)</sub>	Junction to ambient -	to ambient - FR4 using JESD51-3 board			125		°C/W
R <sub>th(j-a)</sub>	Junction to ambient - FR4 using JESD51-7 board				50		°C/W




WARNING Cancer and Reproductive Harm - www.P65Warnings.ca.gov

### **Environmental Characteristics**

Parameter	Value
Moisture Sensitivity Level	1
ESD Classification (HBM)	1B

### **Reference Application**

The TBU® devices are general use protectors used in a wide variety of applications, including telecommunications, industrial communications and automotive battery management systems. The maximum voltage rating of the TBU® device should never be exceeded. Where necessary, an OVP device should be employed to limit the maximum voltage. A cost-effective protection solution combines Bourns® TBU® protection devices with a pair of Bourns® TISP® Overvoltage Protectors or MOVs. For bandwidth sensitive applications, a Bourns® GDT may be substituted for the MOV.



### **Basic TBU Operation**


The TBU® device, constructed using MOSFET semiconductor technology, placed in the system circuit will monitor the current with the MOSFET detection circuit triggering to provide an effective barrier behind which sensitive electronics are not exposed to large voltages or currents during transient events. When operated, the TBU® device will limit the current to less than the l<sub>trigger</sub> value within the t<sub>block</sub> duration. If voltage above V<sub>reset</sub> is continuously sustained, the TBU® device will subsequently reduce the current to a quiescent current level within a period of time that is dependent upon the applied voltage.


After the surge, the TBU® device resets when the voltage across the TBU® device falls to the  $V_{reset}$  level. The TBU® device will automatically reset on lines which have no DC bias or have DC bias below  $V_{reset}$  (such as unpowered signal lines).

# TBU-DF Series - TBU® High-Speed Protectors


### **Performance Graphs**

### **Typical V-I Characteristics**







### **Power Derating Curve**



## Normalized Resistance vs. Temperature



### **Product Dimensions**



Dim.	Min.	Nom.	Max.			
Α	<u>5.40</u>	<u>5.50</u>	<u>5.60</u>			
	(.213)	(.217)	(.220)			
В	6.40	6.50	6.60			
	(.252)	(.256)	(.260)			
С	<u>0.80</u>	<u>0.90</u>	1.00			
	(.031)	(.035)	(.039)			
D	<u>0.00</u> (.000)		<u>0.05</u> (.002)			
E	0.20 (.008) REF.					
F	1.90	<u>2.00</u>	2.10			
	(.075)	(.079)	(.083)			
G	1.75	1.85	1.95			
	(.069)	(.073)	(.077)			
Н	<u>0.65</u>	<u>0.70</u>	0.75			
	(.026)	(.028)	(.030)			
ı	0.70	0.80	0.90			
	(.028)	(.031)	(.035)			
J	<u>0.30</u>	<u>0.35</u>	<u>0.40</u>			
	(.012)	(.014)	(.016)			
К	0.25	0.30	0.35			
	(.010)	(.012)	(.014)			
L	<u>0.75</u>	<u>0.80</u>	<u>0.85</u>			
	(.030)	(.031)	(.033)			

Pad #	Pin Out
1	Line 1 In/Out
2	NU (Not Used)
3	Line 1 In/Out
4	Line 2 In/Out
5	NU (Not Used)
6	Line 2 In/Out

### NOTES:

- Pin 1 Indicator is laser marked; radius and location within the Pin 1 terminal.
  - Pin 1 dot size:  $0.500 \pm 0.125$  mm /  $(.020 \pm .005$  in.).
- Pin 2 and 5 are NU (Not Used) and must be left unconnected; do not connect to In/Out lines, do not connect to system Ground.
- 3. Coplanarity on exposed pads shall not exceed 0.08 mm / (.003 in.).
- 4. Warpage shall not exceed 0.10 mm / (.004 in.) on all surfaces.
- 5. Exposed tie bars at package side are not plated.


# TBU-DF Series - TBU® High-Speed Protectors

# BOURNS

### **Recommended Pad Layout**

TBU® High-Speed Protectors have a 100 % matte-tin termination finish. For improved thermal dissipation, the recommended layout uses PCB copper areas which extend beyond the exposed solder pad. The exposed solder pads should be defined by a solder mask which matches the pad layout of the TBU® device in size and spacing. It is recommended that they should be the same dimension as the TBU® pads but if smaller solder pads are used, they should be centered on the TBU® package terminal pads and not more than 0.10-0.12 mm (0.004-0.005 in.) smaller in overall width or length. Solder pad areas should not be larger than the TBU® pad sizes to ensure adequate clearance is maintained. The recommended stencil thickness is 0.10-0.12 mm (0.004-0.005 in.) with a stencil opening size 0.025 mm (0.0010 in.) less than the solder pad size. Extended copper areas beyond the solder pad significantly improve the junction to ambient thermal resistance, resulting in operation at lower junction temperatures with a corresponding benefit of reliability. All pads should soldered to the PCB, including pads marked as NC or NU but no electrical connection should be made to these pads. Care should be taken to assure no resistive path exists between the NC or NU pins to any other point to avoid


unexpected performance issues. For minimum parasitic capacitance, it is recommended that signal, ground or power signals are not routed beneath any pad. For minimum parasitic capacitance, it is recommended that signal, ground or power signals are not routed beneath any pad.



Dark grey areas show added PCB copper area for better thermal resistance.

### **Reflow Profile**

Profile Feature	Pb-Free Assembly
Average Ramp-Up Rate (Tsmax to Tp)	3 °C/sec. max.
Preheat - Temperature Min. (Tsmin) - Temperature Max. (Tsmax) - Time (tsmin to tsmax)	150 °C 200 °C 60-180 sec.
Time maintained above: - Temperature (TL) - Time (tL)	217 °C 60-150 sec.
Peak/Classification Temperature (Tp)	260 °C
Time within 5 °C of Actual Peak Temp. (tp)	20-40 sec.
Ramp-Down Rate	6 °C/sec. max.
Time 25 °C to Peak Temperature	8 min. max.



### **How to Order** TBU - DF xxx - yyy - WH TBU® Product Series DF = Dual Bidirectional Series Impulse Voltage Rating 055 = 550 V 085 = 850 VTrigger Current 050 = 50 mA300 = 300 mA100 = 100 mA500 = 500 mA200 = 200 mAHold to Trip Ratio Suffix W = Hold to Trip Ratio Package Suffix H = DFN Package

# FXXXX S DIGIT PRODUCT CODE: 1ST ALPHA CHARACTER INDICATES PRODUCT FAMILY: F 18U-DF SERIES 2MA S ARD DIGITS INDICATE IMPULSE VOLTAGE. 4TH & 5TH DIGITS INDICATE TRIGGER CURRENT. MANUFACTURING DATE CODE: 1ST DIGIT INDICATE THE WEEK NUMBER. 4TH & 5TH DIGITS INDICATE THE WEEK NUMBER.

**Typical Part Marking** 


Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

# TBU-DF Series - TBU® High-Speed Protectors

# BOURNS

### **Packaging Specifications**



В D G Ν Ref. Min. Max. Min. Max. Min. Max. Min. Max. Ref. 328.5 331 2.0 2.4 12.8 13.5 17.0 17.4 16.5 100 ± 1.5 (0.690)(12.93)(13.05)(0.079)(0.094)(0.504)(.531)(0.669)(0.650) $\overline{(3.94 \pm 0.059)}$ 

Α	0	В	80	D	0	D	1			F	•
Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	max.
5.75 (0.224)	5.95 (0.234)	6.75 (0.266)	6.95 (0.274)	1.5 (0.059)	1.6 (0.063)	1.5 (0.059)	-	1.65 (0.065)	1.85 (0.073)	7.4 (0.291)	$\frac{7.6}{(0.299)}$
K <sub>0</sub>		F	•	P	0	P	2	F	3	1	
Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.
1.05 (0.041)	1.25 (0.049)	7.9 (0.311)	8.1 (0.319)	3.9 (0.159)	4.1 (0.161)	1.9 (0.075)	2.1 (0.083)	0 (0)	$\frac{0.5}{(.020)}$	0.25 (0.010)	0.35 (0.014)
	(0.010)	(5.511)	(0.010)	(566)	(561)	(5.57.0)	(3.300)	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \	(.020)	(5.510)	(5.511)

W						
Min.	Max.					
15.7	16.3					
(0.618)	(0.642)					

DIMENSIONS:

MM (INCHES)

# **BOURNS®**

Asia-Pacific: Tel: +886-2 2562-4117 • Email: asiacus@bourns.com

EMEA: Tel: +36 88 885 877 • Email: eurocus@bourns.com

The Americas: Tel: +1-951 781-5500 • Email: americus@bourns.com

www.bourns.com

### REV. 08/19

<sup>&</sup>quot;TBU" is a registered trademark of Bourns, Inc. in the United States and other countries, except Japan. All references to TBU® in this document for use in Japan shall be deemed to be replaced with Bourns® TBU".

Specifications are subject to change without notice.

Users should verify actual device performance in their specific applications.

# **Legal Disclaimer Notice**



This legal disclaimer applies to purchasers and users of Bourns® products manufactured by or on behalf of Bourns, Inc. and its affiliates (collectively, "Bourns").

Unless otherwise expressly indicated in writing, Bourns® products and data sheets relating thereto are subject to change without notice. Users should check for and obtain the latest relevant information and verify that such information is current and complete before placing orders for Bourns® products.

The characteristics and parameters of a Bourns® product set forth in its data sheet are based on laboratory conditions, and statements regarding the suitability of products for certain types of applications are based on Bourns' knowledge of typical requirements in generic applications. The characteristics and parameters of a Bourns® product in a user application may vary from the data sheet characteristics and parameters due to (i) the combination of the Bourns® product with other components in the user's application, or (ii) the environment of the user application itself. The characteristics and parameters of a Bourns® product also can and do vary in different applications and actual performance may vary over time. Users should always verify the actual performance of the Bourns® product in their specific devices and applications, and make their own independent judgments regarding the amount of additional test margin to design into their device or application to compensate for differences between laboratory and real world conditions.

Unless Bourns has explicitly designated an individual Bourns® product as meeting the requirements of a particular industry standard (e.g., ISO/TS 16949) or a particular qualification (e.g., UL listed or recognized), Bourns is not responsible for any failure of an individual Bourns® product to meet the requirements of such industry standard or particular qualification. Users of Bourns® products are responsible for ensuring compliance with safety-related requirements and standards applicable to their devices or applications.

Bourns® products are not recommended, authorized or intended for use in nuclear, lifesaving, life-critical or life-sustaining applications, nor in any other applications where failure or malfunction may result in personal injury, death, or severe property or environmental damage. Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any Bourns® products in such unauthorized applications might not be safe and thus is at the user's sole risk. Life-critical applications include devices identified by the U.S. Food and Drug Administration as Class III devices and generally equivalent classifications outside of the United States.

Bourns expressly identifies those Bourns® standard products that are suitable for use in automotive applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard products in an automotive application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk. If Bourns expressly identifies a sub-category of automotive application in the data sheet for its standard products (such as infotainment or lighting), such identification means that Bourns has reviewed its standard product and has determined that if such Bourns® standard product is considered for potential use in automotive applications, it should only be used in such sub-category of automotive applications. Any reference to Bourns® standard product in the data sheet as compliant with the AEC-Q standard or "automotive grade" does not by itself mean that Bourns has approved such product for use in an automotive application.

Bourns® standard products are not tested to comply with United States Federal Aviation Administration standards generally or any other generally equivalent governmental organization standard applicable to products designed or manufactured for use in aircraft or space applications. Bourns expressly identifies Bourns® standard products that are suitable for use in aircraft or space applications on such products' data sheets in the section entitled "Applications." Unless expressly and specifically approved in writing by two authorized Bourns representatives on a case-by-case basis, use of any other Bourns® standard product in an aircraft or space application might not be safe and thus is not recommended, authorized or intended and is at the user's sole risk.

The use and level of testing applicable to Bourns® custom products shall be negotiated on a case-by-case basis by Bourns and the user for which such Bourns® custom products are specially designed. Absent a written agreement between Bourns and the user regarding the use and level of such testing, the above provisions applicable to Bourns® standard products shall also apply to such Bourns® custom products.

Users shall not sell, transfer, export or re-export any Bourns® products or technology for use in activities which involve the design, development, production, use or stockpiling of nuclear, chemical or biological weapons or missiles, nor shall they use Bourns® products or technology in any facility which engages in activities relating to such devices. The foregoing restrictions apply to all uses and applications that violate national or international prohibitions, including embargos or international regulations. Further, Bourns® products and Bourns technology and technical data may not under any circumstance be exported or re-exported to countries subject to international sanctions or embargoes. Bourns® products may not, without prior authorization from Bourns and/or the U.S. Government, be resold, transferred, or re-exported to any party not eligible to receive U.S. commodities, software, and technical data.

To the maximum extent permitted by applicable law, Bourns disclaims (i) any and all liability for special, punitive, consequential, incidental or indirect damages or lost revenues or lost profits, and (ii) any and all implied warranties, including implied warranties of fitness for particular purpose, non-infringement and merchantability.

For your convenience, copies of this Legal Disclaimer Notice with German, Spanish, Japanese, Traditional Chinese and Simplified Chinese bilingual versions are available at:

Web Page: http://www.bourns.com/legal/disclaimers-terms-and-policies

PDF: http://www.bourns.com/docs/Legal/disclaimer.pdf