

## VPU series

### VPU II 4W+G WYE 347V R

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



Similar to illustration

Weidmüller VPU I (Type I), VPU II (Type II) and VPU III (Type III) surge protection products effectively reduce the interference coupling that can occur from transient surge voltages, even significantly below the limits prescribed by insulation co-ordination according to EN 60664-3 / DIN VDE 0110. This means that the whole installation is exposed to fewer malfunctions. The arrestors are co-ordinated using technical means. This means that decoupling between types I, II and III is not necessary. The arrestors are tested according to product standard IEC 61643-11 / DIN EN 61643-11 and can be installed in systems according to IEC 61643-12 / VDE V0675-6-12 and IEC 62305-4 / VDE 0185-4. This lightning and surge protection device is suited for installation in power supply systems for the US market in accordance with UL 1449 Ed.4. Weidmüller offers different products depending on the particular mains network type and voltage level.



#### General ordering data

Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2020-05-01
Type	VPU II 4W+G WYE 347V R
Order No.	<a href="#">2025140000</a>
Version	Surge voltage arrester, Low voltage, with remote contact, TN-S( $U_0 \leq 120/208$ V)
GTIN (EAN)	4050118404913
Qty.	1 pc(s).
Alternative product	<a href="#">2591280000</a>

**VPU series**  
**VPU II 4W+G WYE 347V R**
**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	72 mm	Width (inches)	2.835 inch
Height	106 mm	Height (inches)	4.173 inch
Depth	69 mm	Depth (inches)	2.717 inch
Mounting dimension - height	75 mm	Net weight	536 g

**Temperatures**

Humidity	5 - 95% rel. humidity	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...85 °C		

**Rated data UL**

Certificate No. (cURus)	E354261	Continuous voltage $U_C$ , max.	510 V
Rated voltage $U_N$	120 / 240 undefined	Rated Voltage $U_N$	347 V
Test Voltage 39.1 (UL 1449)	600 V	VPR (L/N-PE)	1,800 V
MCOV (L/N-PE)	510 Vac	SCCR	200 kA
$I_n$	20 kA	Category	SPD TYPE 1CA/2CA

**Connection data, remote alert**

Connection type	PUSH IN	Stripping length	8 mm
Cross-section for connected wire, solid core, min.	0.14 mm <sup>2</sup>	Cross-section for connected wire, solid core, min. (AWG)	AWG 25
Cross-section for connected wire, solid core, max.	1.5 mm <sup>2</sup>	Cross-section for connected wire, solid core, max. (AWG)	AWG 15

**General data**

Colour	black, orange	Design	Installation housing; 4TE, Insta IP 20
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20
Rail	TS 35	Segment	Power distribution
UL 94 flammability rating	V-0	Version	with remote contact

**Insulation coordination acc. to EN 50178**

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

**Rated data IEC / EN**

Discharge current $I_{max}$ (8/20µs) wire-PE	40 kA	Discharge current $I_n$ (8/20µs) wire-PE	20 kA
Follow-on current extinguishing capability $I_{fi}$	Not available due for technical reasons	Fuse	125 A gL > (if back up fuse > 125 A)
Low voltage network	TN-S( $U_0 \leq 120/208$ V)	Max. continuous voltage, $U_c$ (AC)	510 V
Protection level $U_p$ at $I_N$ (L/N-PE)	$\leq 2.1$ kV	Requirements category acc. to IEC 61643-11	Type II
Requirements class, acc. to EN 61643-11	T2	Response time	$\leq 25$ ns
Short-circuit current rating $I_{SCCR}$	25 kA	Signalling contact	250 V 1A 1CO
Voltage type	AC		

Creation date August 22, 2019 3:07:24 PM CEST

## Data sheet

### VPU series VPU II 4W+G WYE 347V R

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Connection data

Type of connection	Screw connection	Stripping length, rated connection	15 mm
Tightening torque, min.	2 Nm	Tightening torque, max.	3 Nm
Wire connection cross section AWG, min.	AWG 14	Wire connection cross section AWG, max.	AWG 0
Wire cross-section, solid, min.	4 mm <sup>2</sup>	Wire cross-section, solid, max.	16 mm <sup>2</sup>
Wire connection cross-section, finely stranded, min.	2.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	25 mm <sup>2</sup>
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	2.5 mm <sup>2</sup>	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	25 mm <sup>2</sup>
Connection cross-section, stranded, min.	4 mm <sup>2</sup>	Connection cross-section, stranded, max.	50 mm <sup>2</sup>

### Ratings IECEx/ATEX/cUL

cUL certificate	UL 1449 ED.4 Certificate
-----------------	--------------------------

### Classifications

ETIM 3.0	EC000941	ETIM 5.0	EC000510
ETIM 6.0	EC000941	UNSPSC	30-21-19-21
eClass 5.1	27-13-08-01	eClass 6.2	27-13-08-02
eClass 7.1	27-14-02-01	eClass 8.1	27-14-02-01
eClass 9.0	27-13-08-05	eClass 9.1	27-13-08-05

### Approvals

Approvals



ROHS	Conform
------	---------

### Downloads


Approval/Certificate/Document of Conformity	<a href="#">EAC VPU SERIES</a> <a href="#">CE PAPER</a> <a href="#">Declaration of Conformity</a>
Engineering Data	<a href="#">STEP</a>
User Documentation	<a href="#">Instruction sheet</a>

**VPU series**  
**VPU II 4W+G WYE 347V R**


**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Drawings**

**Electric symbol**



Schematic circuit diagram UL



Schematic circuit diagram IEC / EN