
muRata Inductor Data Sheet

LQH2HPN2R2MDR# "#" indicates a package specification code.



< List of part numbers with package codes > LQH2HPN2R2MDRL



Notes

When rated current is applied to the products, inductance will be within $\pm 30\%$ of initial inductance value range.

Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.

When rated current is applied to the products, the self-temperature rise shall be limited to $40 \,^{\circ}$ C max. (ambient temperature $85 \,^{\circ}$ C).

When rated current is applied to the products, the self-temperature rise shall be limited to 20 °C max. (ambient temperature 85 °C to 105 °C).

References

Packaging code	Specifications	Minimum quantity
L	φ180mm Embossed taping	4000

Mass (Typ.)	
1 piece	0.010g

Specifications

Inductance	2.2µH ±20%
Inductance test frequency	1MHz
Rated current (Isat) (Based on Inductance change)	850mA
Rated current (Itemp) (Based on Temperature rise)	820mA(Ambient temp.85°C) 500mA(Ambient temp.105°C)
Max. of DC resistance	0.408Ω
Avg. of DC resistance	0.34Ω±20%
Self resonance frequency (min.)	50MHz
Operating temperature range (Self-temperature rise is included)	-40°C to 125°C
Operating temperature range (Self-temperature rise is not included)	-40°C to 105°C
Class of magnetic shield	Magnetic Resin
Series	LQH2HPN_DR
	1 of 2

🔔 Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued


without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Chart of characteristic data (The charts below may show another part number which shares its characteristics.)



2 of 2

🔔 Attention

0

0

LQH2HPN2R2MDR

 This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
This datasheet has only typical specifications because there is no space for detailed specifications.

1600

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

800

Current[mA]

1200

muRata Murata Manufacturing Co., Ltd.

400