


# LQH2HPN6R8MDR#

# indicates a package specification code.



< List of part numbers with package codes >  
LQH2HPN6R8MDRL

## Shape



L size	2.5 ±0.1mm
W size	2.0 ±0.1mm
T size	0.55 ±0.05mm
Size code in inch (mm)	1008 (2520)

## Notes

When rated current is applied to the products, inductance will be within ±30% of initial inductance value range.  
 Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.  
 When rated current is applied to the products, the self-temperature rise shall be limited to 40°C max. (ambient temperature 85°C).  
 When rated current is applied to the products, the self-temperature rise shall be limited to 20°C max. (ambient temperature 85°C to 105°C).

## References

Packaging code	Specifications	Minimum quantity
L	φ 180mm Embossed taping	4000






Mass (Typ.)	
1 piece	0.010g

## Specifications

Inductance	6.8μH ±20%
Inductance test frequency	1MHz
Rated current (I <sub>sat</sub> ) (Based on Inductance change)	550mA
Rated current (I <sub>temp</sub> ) (Based on Temperature rise)	490mA(Ambient temp.85°C) 300mA(Ambient temp.105°C)
Max. of DC resistance	1.2Ω
Avg. of DC resistance	1.0Ω ±20%
Self resonance frequency (min.)	35MHz
Operating temperature range (Self-temperature rise is included)	-40°C to 125°C
Operating temperature range (Self-temperature rise is not included)	-40°C to 105°C
Class of magnetic shield	Magnetic Resin
Series	LQH2HPN_DR

### Attention

- This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



**⚠ Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.