

12Vmax Brushless Combi Drill CXT

HP332DSAJ

Model HP332D is a Cordless hammer driver drill powered by 12V max slide Li-ion battery.



TECHNICAL SPECIFICATIONS

Capacity in Steel	10 mm
Capacity in Wood	28 mm
Chuck Capacity	0.8 – 10 mm
No Load Speed (Hi)	0 - 1,500 rpm
No Load Speed (Lo)	0 - 450 rpm
Blows per Minute (Hi) - ipm	0 - 22,500 ipm
Blows per Minute (Lo) - ipm	0 - 6,750 ipm
Capacity in Masonry	8 mm
Voltage	12 v
Max Torque S/H	21 / 35 Nm
Torque Settings	20 + Drill
Battery Type	Lithium-ion
Battery Quantity (2.0Ah)	2
Vibration K factor	1.5 m/sec ²
Noise sound pressure	82 dB(A)
Noise sound power	93 dB(A)
Noise K factor	3 dB(A)
Net weight	1.1 - 1.3 kg

USER BENEFITS

- Slide type Li-ion battery
- Brushless motor
- Electric brake
- 2 mechanical gears.
- Variable speed control by trigger
- Forward / reverse rotation
- Compact overall length of 168mm
- Equipped with Battery protection circuit: designed to protect the battery from damages due to overdischarge, high temperature or overload current.
- Ergonomic soft grip
- Keyless Chuck
- LED job light
- Belt clip

[Link to product - www.makita.com](http://www.makita.com)



RELATED PRODUCTS

(Recom

STANDARD ACCESSORIES

197396-9

Battery BL1021B



821549-5

MAKPAC CONNECTOR CASE



821550-0

MAKPAC CONNECTOR CASE (TYPE



821551-8

MAKPAC CONNECTOR CASE (TYPE



821552-6

MAKPAC CONNECTOR CASE (TYPE



DC10SB

12Vmax Fast Charger

OTHER