



# 18Vx2 Rotary Hammer 40MM BL LXT DHR400ZKU

DHR400 is a 40 mm (1-9/16") cordless rotary hammer powered by two 18V Li-Ion batteries.



## TECHNICAL SPECIFICATIONS

Battery Type	Lithium-ion
Body only machine	✓
Voltage	36 (18V x2) v
Max in concrete (TCT bit)	40 mm
Max in concrete (TCT core)	105 mm
Impact energy	8.0 J
Shank	SDS-MAX
Blows per minute	1450 - 2900 bpm
Noise sound pressure	91 dB(A)
Noise sound power	102 dB(A)
Noise K factor	3 dB(A)
No Load Speed	250 - 500 rpm
Vibration K factor	1.5 m/sec <sup>2</sup>
Vibration: Hammer Drilling	5.0 m/sec <sup>2</sup>
Vibration: Chiselling	4.5 m/sec <sup>2</sup>
Net weight	7.3 - 8.1 kg

## USER BENEFITS

- Auto-Start Wireless System (AWS) - connects to compatible dust extractors with Bluetooth. The dust extractor automatically runs while the switch is on.
- Brushless motor
- Variable speed
- Electric brake
- Soft start
- Constant speed control
- Torque limiter
- LED job light
- "Soft no load" function automatically reduces the motor speed during idling to suppress the vibration of the machine body.
- 2-mode operation: Rotation with hammering / Hammering only

Link to product - [www.makita.com](http://www.makita.com)



# RELATED PRODUCTS

(Recom

## ■ OTHER