

Description

The 415 Ferric Chloride is an etchant solution for printed circuit board and photoengraving processes.

Features and Benefits

- **Photoengraving Grade—42° Baume**
- **Ready to use without dilution**

ENVIRONMENT

RoHS Compliant
No-VOC

Usage Parameters

<i>Properties</i>	<i>Value</i>
Shelf Life	3 y

Temperature Ranges

<i>Properties</i>	<i>Value</i>
Storage Temperature Limits ^{a)}	16 to 27 °C [60 to 80 °F]

a) Cool, dry, and well-ventilated area recommended.

Properties of 415

<i>Properties</i>	<i>Value</i>
Color	Dark red-brown
Odor	Slight iron/acidic
Viscosity for a 40% solution	12 cP
pH	<2
Solution Strength	38 to 42%
Percent (wt/wt) of Hydrochloric Acid (HCl)	<1.0%
Density	41.6% Baume to 45% Baume
Specific Gravity @17.5 °C [63.5 °F]	1.43
Boiling Point	110 °C [230 °F]
Freezing Point	-50 °C [-58 °F]
Crystallization @-26 °C [-15 °F]	37% FeCl ₃
@-12 °C [10 °F]	40% FeCl ₃

Compatibility

Chemical—Ferric chloride reacts strongly with metals.

Storage

Store between 16 and 27 °C [60 and 80 °F] in a dry area. Store in plastic container. Do NOT store in metal containers.

Health and Safety

Please see the 415 **Safety Data Sheet** (SDS) for further details on transportation, storage, handling, safety guidelines, and regulatory compliance.

Application Instructions

For best results, follow the procedure below. If further directions for etching or making a printed circuit board (PCB), consult the photofabrication process guide available free from your dealer.

1. Fully immerse copper board in solution.
2. Agitate until etching action is complete.

To speed up etching:

- Warm the ferric chloride solution between 35 to 55 °C [95 to 131 °F].

ATTENTION! Do NOT heat ferric chloride solution above 55 °C [131 °F].

NOTE: Dilution is not recommended.

Packaging and Supporting Products

<i>Cat. No.</i>	<i>Packaging</i>	<i>Net Volume</i>		<i>Packaged Weight</i>	
415-500ML	Bottle	475 mL	1 pt	7.5 kg	16.5 lb
415-1L	Bottle	945 mL	1.99 pt	9 kg	19.8 lb
415-4L	Bottle	4 L	1.06 gal	6.12 kg	13.4 lb
415-20L	Bottle	20 L	5.3 gal	28.3 kg	62.3 lb

Related Products and Etching Kits

- *Economy Etching Kit:* Cat. No. 416-ES
- *Photofabrication Kit:* Cat. No. 416-K
- *Professional Etching Kit:* Cat. No. 416-E



415 Technical Data Sheet Ferric Chloride

ISO 9001:2008 Registered Quality System. Burlington, Ontario, CANADA SAI Global File: 004008

415-Liquid

Technical Support

Please contact us regarding any questions, suggestions for improvements, or problems with this product. Application notes, instructions and FAQs are located at www.mgchemicals.com.

Email: support@mgchemicals.com

Phone: +(1) 800-340-0772 (Canada, Mexico & USA)

+ (1) 905-331-1396 (International)

+ (44) 1663 362888 (UK & Europe)

Fax: +(1) 905-331-2862 or +(1) 800-340-0773

Mailing address: **Manufacturing & Support**
1210 Corporate Drive
Burlington, Ontario, Canada
L7L 5R6

Head Office
9347-193rd Street
Surrey, British Columbia, Canada
V4N 4E7

Disclaimer

This information is believed to be accurate. It is intended for professional end users who have the skills required to evaluate and use the data properly. *M.G. Chemicals Ltd.* does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.