

Transistor NPN, TO-3

multicomp^{PRO}



RoHS
Compliant

Description:

Complementary silicon power transistors.

The power transistors designed for high power audio, disk head positions and other linear applications.

These devices can also be used in power switching circuits such as relay or solenoid drivers. DC-DC converters or inverters.

Features:

- Pb-free packages
- High safe operating area (100% tested) 150W at 100V
- Completely characterized for linear operation
- High DC current gain and low saturation voltage
- $h_{FE} = 15$ (Min.) at 8A, 4V
- $V_{CE(sat)} = 1.4V$ (Max.) at $I_C = 8A$, $I_B = 0.8A$
- For low distortion complementary designs

Maximum Ratings (Note 1)

Rating	Symbol	Value	Unit
Collector-Emitter Voltage	V_{CEO}	140	V DC
Collector-Emitter Voltage	V_{CEX}	160	
Collector-Base Voltage	V_{CBO}		
Emitter-Base Voltage	V_{EBO}	7	
Collector Current -Continuous -Peak (Note 2)	I_C	16 30	A DC
Base Current -Continuous -Peak (Note 2)	I_B	4 15	
Total Device Dissipation at $T_A = 25^\circ C$ Derate above $25^\circ C$	P_D	150 0.855	W W/ $^\circ C$
Operating and Storage Junction Temperature Range	T_J, T_{stg}	-65 to +200	$^\circ C$

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.

1. Indicates JEDEC registered data.
2. Pulse test: pulse width = 5 μs , duty cycle $\leq 10\%$.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp^{PRO}

Transistor

NPN, TO-3

multicomp PRO

Thermal Characteristics

Characteristics	Symbol	Max.	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	1.17	$^{\circ}C/W$

Electrical Characteristics ($T_c = 25^{\circ}C$ unless otherwise noted)

Characteristic	Symbol	Min.	Max.	Unit
Off Characteristics (Note 3)				
Collector-Emitter Sustaining Voltage (Note 4) ($I_C = 0.2A$ DC, $I_B = 0$)	$I_{EO(sus)}$	140	-	V DC
Collector-Emitter Sustaining Voltage (Note 4) ($I_C = 0.1A$ DC, $V_{EB(off)} = 1.5$ V DC, $R_{BE} = 100\Omega$)	$V_{CEX(sus)}$	160	-	
Collector-Emitter Sustaining Voltage ($I_C = 0.2A$ DC, $R_{BE} = 100\Omega$)	$V_{CER(sus)}$	150	-	
Collector Cut off Current (Note 4) ($V_{CE} = 120V$ DC, $I_B = 0$)	I_{CEO}	-	10	mA DC
Collector Cut off Current (Note 4) ($V_{CE} = 140V$ DC, $V_{BE(off)} = 1.5V$ DC) ($V_{CE} = 140V$ DC, $V_{BE(off)} = 1.5V$ DC, $T_C = 150^{\circ}C$)	I_{CEX}	-	2 10	
Collector Cut off Current (Note 4) ($V_{CE} = 140V$ DC, $I_B = 0$)	I_{CBO}	-	2	
Emitter Cut off Current (Note 4) ($V_{EB} = 5V$ DC $I_C = 0$)	I_{EBO}	-	5	

On Characteristic (Note 3)

DC Current Gain ($I_C = 8A$ DC, $V_{CE} = 4V$ DC) (Note 4) ($I_C = 16A$ DC, $V_{CE} = 4V$ DC)	h_{FE}	15 5	60	-
Collector-Emitter Saturation Voltage ($I_C = 8A$ DC, $I_B = 800mA$ DC) (Note 4) ($I_C = 16A$ DC, $I_B = 3.2A$ DC)	$V_{CE(sat)}$	-	1.4 4	V DC
Base-Emitter On Voltage (Note 4) ($I_C = 8A$ DC, $V_{CE} = 4V$ DC)	$V_{BE(on)}$	-	2.2	

Dynamic Characteristics

Magnitude of Common-Emitter Small-Signal, Short-Circuit, Forward Current Transfer Ratio ($I_C = 1A$, $f = 50kHz$)	$ h_{fe} $	4	-	-
Small-Signal Current Gain (Note 4) ($I_C = 1A$ DC, $V_{CE} = 4V$ DC, $f = 1$ kHz)	h_{fe}	40	-	-

Second Breakdown Characteristics

Second Breakdown Collector Current with Base Forward Biased $t = 1s$ (non-repetitive), $V_{CE} = 100V$	$I_{s/b}$	1.5		A DC
---	-----------	-----	--	------


3. Pulse Test: Pulse Width = 300 μ s, Duty Cycle \leq 2%.

4. Indicates JEDEC Registered Data.


Transistor NPN, TO-3

multicomp **PRO**


DC Current Gain




Forward Bias Safe Operating Area




Collector Saturation Region



"On" Voltage



Power Derating




There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate $I_C - V_{CE}$ limits of the transistor that must be observed for reliable operation i.e., the transistor must not be subjected to greater dissipation than curves indicate. The data is based on $T_J (PK) = 200^\circ C$; T_C is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided $T_J (PK) < 200^\circ C$. At high case temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown.

multicomp **PRO**

Transistor NPN, TO-3

multicomp PRO

(TO-3)



Dimensions	Min.	Max.
A	1.55 (39.37)	Reference
B	-	1.05 (26.67)
C	0.25 (6.35)	0.335 (8.51)
D	0.038 (0.97)	0.043 (1.09)
E	0.055 (1.4)	0.07 (1.77)
G	0.43 (10.92)	BSC
H	0.215 (5.46)	BSC
K	0.44 (11.18)	0.48 (12.19)
L	0.665 (16.89)	BSC
N	-	0.83 (21.08)
Q	0.151 (3.84)	0.165 (4.19)
U	1.187 (30.15)	BSC
V	0.131 (3.33)	0.188 (4.77)

Dimensions : Inches (Millimetres)

Style 1:

- Pin 1. Base
- 2. Emitter
- Collector (Case)

Part Number Table

Description	Part Number
Transistor, NPN, TO-3	2N3773

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO