



Note: This datasheet may be out of date

 $\underline{ \text{Please download the latest datasheet of NCP03XH103F05RL from the official website of Murata Manufacturing} \\$ 

https://www.murata.com/en-eu/products/productdetail?partno=NCP03XH103F05RL

### NCP03XH103F05RL












### Appearance & Shape







- 1. Excellent solderability and high stability in environment
- 2. Excellent long time aging stability
- 3. High accuracy in resistance and B-Constant
- 4. Reflow soldering possible
- 5. Lead is not contained in the product.
- 6. NCP series are recognized by UL/cUL (UL1434, File No.E137188).



Limited Usage	Mobile Application, Tablet PC, Wearable
Other Usage	Temperature compensation for transistor, IC and crystal oscillator in mobile communications Temperature sensor for rechargeable batteries



# Packaging Information

Packaging	Specifications	Minimum Order Quantity
RL	180mm Paper Tape	15000

1 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated :2019/11/25



Note: This datasheet may be out of date

 $\underline{ \text{Please download the latest datasheet of NCP03XH103F05RL from the official website of Murata Manufacturing} \\$ Co., Ltd. https://www.murata.com/en-eu/products/productdetail?partno=NCP03XH103F05RL

# NCP03XH103F05RL



Resistance (25°C)	10kΩ
Resistance Value Tolerance (at 25°C)	±1%
B-Constant (25/50°C)	3380K
B-Constant (25/50°C) Tolerance	±1%
B-Constant(25/80°C)(Reference Value)	3428K
B-Constant(25/85°C)(Reference Value)	3434K
B-Constant(25/100°C)(Reference Value)	3455K
Max. Voltage	5V
Maximum Operating Current (25°C)	0.1mA
Typical Dissipation Constant (25°C)	1mW/°C
Operating Temperature Range	-40°C to 125°C
Size Code (in mm)	0.6x0.3mm
Shape	SMD
Mass	0.00026g

2 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering




URL: https://www.murata.com/


Last updated :2019/11/25

https://www.murata.com/en-eu/products/productdetail?partno=NCP03XH103F05RL

# NCP03XH103F05RL







Resistance-Temperature Characteristics

Maximum Operating Voltage Reduction Characteristics

3 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/