



Note: This datasheet may be out of date

Please download the latest datasheet of PRG21BB220MB1RK from the official website of Murata Manufacturing https://www.murata.com/en-eu/products/productdetail?partno=PRG21BB220MB1RK

PRG21BB220MB1RK












Appearance & Shape





| Part Number | Dimensions (mm) | | | | |
|-------------|-----------------|----------|----------|-------------|----------|
| rait Number | L | W | T | е | g |
| PRG15_RC | 1.0±0.05 | 0.5±0.05 | 0.5±0.05 | 0.15 to 0.4 | - |
| PRG18_RB | 1.6±0.15 | 0.8±0.15 | 0.8±0.15 | 0.1 to 0.6 | - |
| PRG21_RA | 2.0±0.2 | 1.25±0.2 | 0.9±0.2 | 0.2 min. | 0.5 min. |
| PRG21_RK | 2.0±0.2 | 1.25±0.2 | 1.25±0.2 | 0.2 min. | 0.5 min. |



Features

1.Rapid operation to protect the circuit in an overcurrent condition abnormality such as a short circuit.

By removing the overcurrent condition, these products automatically return to the initial condition and can be used repeatedly.

- 2. Suitable for countermeasure to short circuit test in safety standard
- 3. Stable resistance after operation due to ceramic PTC
- 4. Similar size (0603 size) is possible due to the large capacity for electric power.
- 5. Possible to use these products as current limiting resistors with overcurrent protection functions
- 6.SMD type is helpful for miniaturizing circuits because of its small size and light weight
- 7.Lead is not contained in the terminations





Consumer Grade



Packaging Information

| Packaging | Specifications | Minimum Order Quantity | |
|-----------|---------------------|---------------------------|--|
| RK | 180mm Embossed Tape | 3000 | |

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated :2019/11/25

Note: This datasheet may be out of date

 $\underline{ \text{Please download the latest datasheet of PRG21BB220MB1RK from the official website of Murata Manufacturing} \\$ Co., Ltd.
https://www.murata.com/en-eu/products/productdetail?partno=PRG21BB220MB1RK

PRG21BB220MB1RK



| Max. Voltage | 20V |
|---------------------------------------|---------------|
| Hold Current | 30mA |
| Measure Condition of Hold Current | (at +60°C) |
| Hold Current (2) | 44mA |
| Measure Condition of Hold Current (2) | (at +25°C) |
| Trip Current | 91mA |
| Measure Condition of Trip Current | (at +25°C) |
| Trip Current(2) | 115mA |
| Measure Condition of Trip Current(2) | (at -20°C) |
| Max. Current | 1100mA |
| Resistance (25°C) | 22Ω |
| Resistance Value Tolerance (at 25°C) | ±20% |
| Operating Temperature Range | -20°C to 60°C |
| Size Code (in mm) | 2.0x1.25mm |
| Shape | SMD |
| Mass | 0.017g |

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/


Last updated :2019/11/25


Note: This datasheet may be out of date

https://www.murata.com/en-eu/products/productdetail?partno=PRG21BB220MB1RK


PRG21BB220MB1RK







Resistance-Temperature Charac.



Operating Time (Typical Curve)

Protective Threshold Current Range

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

3 of 3

Last updated :2019/11/25