


# PTGL14ARR15M1B51B0

In Production Recommended RoHS REACH

## Appearance & Shape



(in mm)

## Features

1. Best suited to meet the requirements for power supplies and motor protection. Error-free operation is assured by rush current.
2. Circuit is protected until current is turned off.
3. Restores the original low resistance value automatically once the overload is removed.
4. Non-contact design leads to long life and no noise.  
Durable and strong against mechanical vibration and shock because it is a solid element.

## Applications

Limited Usage	Consumer Grade
---------------	----------------

## Packaging Information

Packaging	Specifications	Minimum Order Quantity
B0	Bulk(Bag)	300

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2. This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# PTGL14ARR15M1B51B0



## Specifications

Max. Voltage	16V	F: Lead Space	5mm
Hold Current	1200mA	d: Lead Diameter	0.6mm
Measure Condition of Hold Current	(at +60°C)	Shape	Lead
Hold Current (2)	1545mA	Mass	0.77g
Measure Condition of Hold Current (2)	(at +25°C)		
Trip Current	2855mA		
Measure Condition of Trip Current	(at +25°C)		
Trip Current(2)	3360mA		
Measure Condition of Trip Current(2)	(at -10°C)		
Max. Current	10A		
Resistance (25°C)	0.15Ω		
Resistance Value Tolerance (at 25°C)	±20%		
Power Consumption(typ)	2.3W		
Operating Temperature Range	-10°C to 60°C		
D: Outer Dimension	13.5mm		
Thickness	3.5mm		
H: Height	18.5mm		

### Attention


1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# PTGL14ARR15M1B51B0


## Product Data



Resistance-Temperature Charac.



Protective Threshold Current Range



Operating Time (Typical Curve)

**Attention**

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.  
2. This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.