



**Miniature SOP8-pin type  
Low CxR High load  
voltage of 250V**

**PhotoMOS®  
RF SOP 2 Form A CxR  
(AQW223R2S)**



mm inch



### FEATURES

1. **With high load voltage of 250V, low output capacitance and low on-resistance.**  
Output capacitance ( $C_{out}$ ): Typ. 33 pF  
On-resistance ( $R_{on}$ ): Typ. 11Ω
2. **2-channel (Form A) in miniature SOP8-pin package**  
(W) 4.4 × (L) 9.37 × (H) 2.1 mm  
(W) .173× (L) .369 × (H) .083 inch
3. **Low-level off-state leakage current of Typ. 0.03 nA**
4. **Controls low-level analog signals**

**RoHS compliant**

### TYPICAL APPLICATIONS

1. **Measuring and testing equipment**  
IC tester, Liquid crystal driver tester, Semiconductor performance tester, Bear board tester, In-circuit tester, Function tester, etc.
2. **Telecommunication and broadcasting equipment**
3. **Medical equipment**
4. **Multi-point recorder**  
Data logger, Warping and Thermocouple, etc.

### TYPES

	Output rating*		Package	Part No.		Packing quantity		
	Load voltage	Load current		Tape and reel packing style		Tube	Tape and reel	
				Tube packing style	Picked from the 1/2/3/4-pin side			
AC/DC dual use	250V	0.14A	SOP8-pin	AQW223R2S	AQW223R2SX	AQW223R2SZ	1 tube contains: 50 pcs. 1 batch contains: 1,000 pcs.	

\* Indicate the peak AC and DC values.

Note: The packing style indicator "X" or "Z" is not marked on the device.

### RATING

#### 1. Absolute maximum ratings (Ambient temperature: 25°C 77°F)

	Item	Symbol	AQW223R2S	Remarks
Input	LED forward current	$I_F$	50 mA	
	LED reverse voltage	$V_R$	5 V	
	Peak forward current	$I_{FP}$	1 A	$f = 100$ Hz, Duty factor = 0.1%
	Power dissipation	$P_{in}$	75 mW	
Output	Load voltage (peak AC)	$V_L$	250 V	
	Continuous load current	$I_L$	0.14 A (0.17 A)	Peak AC, DC ( ): in case of using only 1a (1 channel)
	Peak load current	$I_{peak}$	0.42 A	100 ms (1 shot), $V_L = DC$
	Power dissipation	$P_{out}$	600 mW	
Total power dissipation		$P_T$	650 mW	
I/O isolation voltage		$V_{iso}$	1,500 Vrms	
Ambient temperature	Operating	$T_{opr}$	-40 to +85°C -40 to +185°F	(Non-icing at low temperatures)
	Storage	$T_{stg}$	-40 to +100°C -40 to +212°F	


# RF SOP 2 Form A CxR (AQW223R2S)

## 2. Electrical characteristics (Ambient temperature: 25°C 77°F)

Item		Symbol	AQW223R2S	Condition
Input	LED operate current	I <sub>Fon</sub>	0.5mA	I <sub>L</sub> =Max.
	Maximum		3.0mA	
Output	LED turn off current	I <sub>off</sub>	0.1mA	I <sub>L</sub> =Max.
	Typical		0.45mA	
Transfer characteristics	LED dropout voltage	V <sub>F</sub>	1.32V (1.14V at I <sub>F</sub> =5mA)	I <sub>F</sub> =50mA
	Maximum		1.5V	
Output	On resistance	R <sub>on</sub>	11Ω	I <sub>F</sub> =5mA I <sub>L</sub> =Max.
	Maximum		15Ω	
Transfer characteristics	Output capacitance	C <sub>out</sub>	33pF	I <sub>F</sub> =0mA f=1 MHz V <sub>B</sub> =0V
	Maximum		40pF	
Transfer characteristics	Off state leakage current	I <sub>Leak</sub>	0.03nA	I <sub>F</sub> =0mA V <sub>L</sub> =Max.
	Maximum		*10nA	
Transfer characteristics	Turn on time**	T <sub>on</sub>	0.15ms	I <sub>F</sub> =5mA I <sub>L</sub> =Max.
	Maximum		0.5ms	
Transfer characteristics	Turn off time**	T <sub>off</sub>	0.05ms	I <sub>F</sub> =5mA I <sub>L</sub> =Max.
	Maximum		0.2ms	
Transfer characteristics	I/O capacitance	C <sub>iso</sub>	0.8pF	f=1MHz V <sub>B</sub> =0V
	Maximum		1.5pF	
Initial I/O isolation resistance		R <sub>iso</sub>	1,000MΩ	500V DC

\*Available as custom orders (1 nA or less)

\*\*Turn on/Turn off time



## 3. Recommended operating conditions (Ambient temperature: 25°C 77°F)

Please use under recommended operating conditions to obtain expected characteristics.

Item	Symbol	Number of used channels	Min.	Max.	Unit
LED current	I <sub>F</sub>		5	30	mA
AQW223R2S	V <sub>L</sub>		—	125	V
Load voltage (Peak AC)	I <sub>L</sub>	1ch 2ch	—	0.17 0.14	A
Continuous load current					


■ These products are not designed for automotive use.

If you are considering to use these products for automotive applications, please contact your local Panasonic Corporation technical representative.

## REFERENCE DATA


### 1. Load current vs. ambient temperature characteristics

Allowable ambient temperature: -40 to +85°C  
-40 to +185°F




### 2. On resistance vs. ambient temperature characteristics

Measured portion: between terminals 5 and 6, 7 and 8:  
LED current: 5 mA;  
Load voltage: Max. (DC);  
Continuous load current: Max. (DC)




### 3. Turn on time vs. ambient temperature characteristics

LED current: 5 mA;  
Load voltage: Max. (DC);  
Continuous load current: Max. (DC)




**4. Turn off time vs. ambient temperature characteristics**


LED current: 5 mA; Load voltage: Max. (DC);  
Continuous load current: Max. (DC)

**5. LED operate current vs. ambient temperature characteristics**


Load voltage: Max. (DC);  
Continuous load current: Max. (DC)

**6. LED turn off current vs. ambient temperature characteristics**

Load voltage: Max. (DC);  
Continuous load current: Max. (DC)


**7. LED dropout voltage vs. ambient temperature characteristics**

LED current: 5 to 50 mA

**8. Current vs. voltage characteristics of output at MOS portion**


Measured portion: between terminals 5 and 6, 7 and 8;

Ambient temperature: 25°C 77°F


**9. Off state leakage current vs. load voltage characteristics**

Measured portion: between terminals 5 and 6, 7 and 8;


Ambient temperature: 25°C 77°F

**10. Turn on time vs. LED forward current characteristics**


Measured portion: between terminals 5 and 6, 7 and 8;  
Load voltage: Max. (DC);  
Continuous load current: Max. (DC);  
Ambient temperature: 25°C 77°F

**11. Turn off time vs. LED forward current characteristics**

Measured portion: between terminals 5 and 6, 7 and 8;  
Load voltage: Max. (DC);  
Continuous load current: Max. (DC);  
Ambient temperature: 25°C 77°F

**12. Output capacitance vs. applied voltage characteristics**

Measured portion: between terminals 5 and 6, 7 and 8;  
Frequency: 1 MHz, 30mVrms;  
Ambient temperature: 25°C 77°F



"PhotoMOS®", "PhotoMOS" and "PHOTOMOS" are registered trademarks of Panasonic Corporation.

\*Recognized in Japan, the United States, all member states of European Union and other countries.

---

Please contact .....

**Panasonic Corporation**

Electromechanical Control Business Division

■ 1006, Oaza Kadoma, Kadomashi, Osaka 571-8506, Japan  
[industrial.panasonic.com/ac/e/](http://industrial.panasonic.com/ac/e/)

**Panasonic®**

©Panasonic Corporation 2017