

# A16-30-10 220-230V 50Hz / 230-240V 60Hz



A16-30-10 220-230V 50Hz / 230-240V 60Hz Contactor

## General Information

Extended Product Type	A16-30-10 220-230V 50Hz / 230-240V 60Hz
Product ID	1SBL181001R8010
EAN	3471522050809
Catalog Description	A16-30-10 220-230V 50Hz / 230-240V 60Hz Contactor
Long Description	A16 contactors are mainly used for controlling 3-phase motors and generally for controlling power circuits up to 690 V AC or 220 V DC. The contactors can also be used for many other applications such as isolation, capacitor switching, lighting. The A... series 1-stack 3-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 3 main poles, 1 built-in auxiliary contact, front and side-mounted add-on auxiliary contact blocks - Control circuit: AC operated with laminated magnet circuit - Accessories: a wide range of accessories is available.

## Classifications

Object Classification Code	Q
ETIM 4	EC000066 - Magnet contactor, AC-switching
ETIM 5	EC000066 - Magnet contactor, AC-switching
ETIM 6	EC000066 - Power contactor, AC switching
ETIM 7	EC000066 - Power contactor, AC switching
UNSPSC	39121529

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	78 mm
Package Level 1 Depth / Length	76 mm
Package Level 1 Height	47 mm
Package Level 1 Gross Weight	0.34 kg
Package Level 1 EAN	3471522050809
Package Level 2 Units	63 piece
Package Level 2 Gross Weight	21.42 kg
Package Level 3 Units	1220 piece

## Certificates and Declarations (Document Number)

BV Certificate	BV_2634H07559E0
CB Certificate	CB_FR_602227A
CCC Certificate	CCC_2018010304059156 CCC_2004010309130463

CSA Certificate	CSA_1041746
Declaration of Conformity - CE	1SBD250801U1000
DNV Certificate	DNV-GL_TAE00000TX
DNV GL Certificate	DNV-GL_TAE00000TX
EAC Certificate	EAC_RU C-FR ME77 B01010
Environmental Information	1SBD250003E1004
GOST Certificate	GOST_POCCFRME77B07175
Instructions and Manuals	FPTC407721P0001
LOVAG Certificate	LOVAG_FR97039
LR Certificate	LRS_9830011E4
RINA Certificate	RINA_ELE128713XG001
RMRS Certificate	RMRS_0507015250
RoHS Information	1SBD250801U1000
UL Certificate	UL_20160205-E312527-10-2
UL Listing Card	UL_E312527

## Environmental

Ambient Air Temperature	Close to Contactor for Storage -60 ... +80 °C Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 Uc) -40 ... +55 °C Close to Contactor Fitted with Thermal O/L Relay -25 ... +55 °C Close to Contactor without Thermal O/L Relay (Uc) -40 ... +70 °C
Climatic Withstand	acc. to IEC 60068-2-30 and 60068-2-11 - UTE C 63-100 specification II
Maximum Operating Altitude Permissible	3000 m
Resistance to Shock acc. to IEC 60068-2-27	Shock Direction: A 20 K40 Shock Direction: B2 15 K40 Shock Direction: C1 20 K40 Shock Direction: C2 20 K40 Closed, Shock Direction: B1 10 K40 Open, Shock Direction: B1 5 K40
RoHS Status	Following EU Directive 2011/65/EU

## Technical

Number of Main Contacts NO	3
Number of Main Contacts NC	0
Number of Auxiliary Contacts NO	1
Number of Auxiliary Contacts NC	0
Standards	Devices complying with international standards IEC 947-1 / 947-4-1, and European standards EN 60 947-1 / 60 947-4-1. Electromagnetic compatibility (EMC) acc. to amendment A11 to IEC 947-1, EN 60 947-1 and amendment 2 to IEC 947-4-1
Rated Operational Voltage	Main Circuit 690 V
Rated Frequency (f)	Supply Circuit 50 60 Hz
Conventional Free-air Thermal Current ( $I_{th}$ )	acc. to IEC 60947-5-1, $q = 40$ °C 16 A acc. to IEC 60947-4-1, Open Contactors $q = 40$ °C 30 A
Rated Operational Current AC-1 ( $I_e$ )	(690 V) 40 °C 30 A (690 V) 55 °C 27 A (690 V) 70 °C 23 A
Rated Operational Current AC-3 ( $I_e$ )	(220 / 230 / 240 V) 55 °C 17 A (380 / 400 V) 55 °C 17 A (415 V) 55 °C 17 A (440 V) 55 °C 16 A (500 V) 55 °C 14 A (690 V) 55 °C 10 A
Rated Operational Power AC-3 ( $P_e$ )	(220 / 230 / 240 V) 4 KWT (380 / 400 V) 7.5 KWT

	(415 V) 9 KWT (440 V) 9 KWT (500 V) 9 KWT (690 V) 9 KWT
Rated Breaking Capacity AC-3 acc. to IEC 60947-4-1	8 x I <sub>e</sub> AC-3
Rated Making Capacity AC-3 acc. to IEC 60947-4-1	10 x I <sub>e</sub> AC-3
Rated Operational Current AC-15 (I <sub>o</sub> )	(220 / 240 V) 4 A (24 / 127 V) 6 A (380 / 440 V) 3 A (500 V) 2 A (690 V) 2 A
Short-Circuit Protective Devices	Auxiliary Circuit - gG Type Fuses 10 A gG Type Fuses 32 A
Maximum Breaking Capacity	cos phi=0.45 (cos phi=0.35 for I <sub>e</sub> > 100 A) at 440 V 250 A cos phi=0.45 (cos phi=0.35 for I <sub>e</sub> > 100 A) at 690 V 90 A
Maximum Electrical Switching Frequency	AC-1 600 cycles per hour AC-2 / AC-4 300 cycles per hour AC-3 1200 cycles per hour
Rated Operational Current DC-13 (I <sub>o</sub> )	(125 V) 1.1 / 138 A (24 V) 6 / 144 A (250 V) 0.55 / 138 A (48 V) 2.8 / 134 A (72 V) 2 / 144 A
Rated Insulation Voltage (U <sub>i</sub> )	acc. to UL/CSA 600 V acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V
Rated Impulse Withstand Voltage (U <sub>imp</sub> )	8 kV
Maximum Mechanical Switching Frequency	3600 cycles per hour
Rated Control Circuit Voltage (U <sub>c</sub> )	50 Hz 220 ... 230 V 60 Hz 230 ... 240 V
Coil Consumption	Average Holding Value 50 / 60 Hz 8.2 V·A Average Pull-in Value 50 Hz 74 V·A Average Pull-in Value 60 Hz 70 V·A
Operate Time	Between Coil De-energization and NO Contact Opening 4 ... 11 ms Between Coil Energization and NO Contact Closing 10 ... 26 ms
Connecting Capacity Main Circuit	Flexible with Cable End 0.75 ... 2.5 m <sup>2</sup> Rigid Cable 1 ... 4 m <sup>2</sup>
Connecting Capacity Auxiliary Circuit	Flexible with Cable End 0.75 ... 2.5 m <sup>2</sup> Rigid Cable 1 ... 4 m <sup>2</sup>
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20
Connecting Terminals (delivered in open position) Main M 3.5 (+,-) pozidriv 2 screws with cable clamp Poles	
Terminal Type	Screw Terminals

## Dimensions

Product Net Width	44 mm
Product Net Depth / Length	74 mm
Product Net Height	74 mm
Product Net Weight	0.34 kg

## Popular Downloads

Data Sheet, Technical Information	1SBC100122C0202_Ch02
Instructions and Manuals	FPTC407721P0001

## Ordering

---

Minimum Order Quantity	1 piece
Customs Tariff Number	85364900

---

---

## Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors

