<b>muRata</b> Inductor Data S	Sheet			
LQH43NH330J03	#" indicates a package specifica	tion code.		
New In Production Power- train AEC- Q200	125 Cmax. (Ferrite) Reflow RoHS REA	сн		
< List of part numbers with package codes > LQH43NH330J03L , LQH43NH330J03K				
Shape		Note	es	
3.6±0.2 3.2±0.2 A () A		When rated current is applied to the products, self-temperature rise shall be limited to 20 °C max and inductance will be within ±10% of nominal value.		
4.5±0.3 A: 3.5 max.		References		
		Packaging code	Specifications	Minimum quantity
1.0 min. (in mm		L	φ180mm Embossed taping	500
		К	φ330mm Embossed taping	2500
L size	4.5 ±0.3mm			
W size	3.2 ±0.2mm	Mass (Typ.)		
T size	2.6 ±0.2mm	1 piece		0.13g

1812 (4532)

## Specifications

Size code in inch (mm)

Inductance	33μH ±5%
Inductance test frequency	1MHz
Rated current (Itemp) (Based on Temperature rise)	250mA
Max. of DC resistance	0.84Ω
Avg. of DC resistance	0.7Ω±20%
Q (min.)	35
Q test frequency	1MHz
Self resonance frequency (min.)	12MHz
Operating temperature range	-40 to 125°C
Class of magnetic shield Series	No Shield LQH43NH_03

## 🔔 Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

1 of 1