




Power Metal Strip[®] Resistors, Very High Power (1 W), Low Value (down to 0.005 Ω), Surface Mount



DESIGN SUPPORT TOOLS

click logo to get started





FEATURES

 Very high power to foot print size ratio (1 W in 0805 / 2 W in 1206 package)



 All welded construction of the Power Metal Strip[®] resistors is ideal for all types of current sensing, voltage division and pulse applications




• Proprietary processing technique produces extremely low resistance values (down to $0.005~\Omega$)

ROHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

- Sulfur resistance by construction that is unaffected by high sulfur environments
- Solid metal nickel-chrome or manganese- copper alloy resistive element with low TCR (< 20 ppm/°C)
- Very low inductance 0.5 nH to 5 nH
- Excellent frequency response to 50 MHz
- Low thermal EMF (< 3 μV/°C)
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

STANDARD ELECTRICAL SPECIFICATIONS						
GLOBAL MODEL	SIZE	POWER RATING P _{70 °C} W	TOLERANCE ± %	$\begin{array}{c} \textbf{RESISTANCE} \\ \textbf{VALUE RANGE} \\ \Omega \end{array}$	WEIGHT (typical) g/1000 pieces	
WSLP080518	0805	1.0	1.0, 5.0	0.005 to 0.01	4.8	
WSLP120618	1206	2.0	1.0, 5.0	0.005 to 0.012	16.2	



Notes

- (1) WSL Marking (www.vishay.com/doc?30327); WSL Decade Values (www.vishay.com/doc?30117)
- (2) EB (lead (Pb)-free) is a non-standard packaging code designated for 1000 piece reels. The non-standard packaging code is identical to our standard EA (lead (Pb)-free), except that it has a package quantity of 1000 pieces
- (3) Follow link for customization capabilities: www.vishay.com/doc?48163




TECHNICAL SPECIFICATIONS				
PARAMETER	UNIT	RESISTOR CHARACTERISTICS		
Temperature coefficient (1)	ppm/°C	\pm 110 for 5 m Ω to 6.9 m		
remperature coemcient (7		\pm 75 for 7 m Ω to 12 m Ω		
Element TCR (2)	ppm/°C	< 20		
Operating temperature range	°C	-65 to +170		
Maximum working voltage (3)	V	(P x R) ^{1/2}		

Notes

- (1) Component TCR total TCR that includes the TCR effects of the resistor element and the copper terminal
- (2) Element TCR only applies to the alloy used for the resistor element; refer to item 1 in the construction illustration on the following page
- (3) Maximum working voltage the WSL is not voltage sensitive, but is limited by power / energy dissipation and is also not ESD sensitive

DIMENSIONS




Notes

- 3D models available: www.vishav.com/doc?30306
- Surface mount solder profile recommendations: www.vishay.com/doc?31052


MODEL RESISTANCE		DIMENSIONS in inches (millimeters)				SOLDER PAD DIMENSIONS in inches (millimeters)		
	RANGE (Ω)	L	W	Н	Т	а	b	I
WSLP080518	0.005 to 0.01	0.080 ± 0.010 (2.03 ± 0.254)	0.050 ± 0.010 (1.27 ± 0.254)	0.013 ± 0.010 (0.330 ± 0.254)	0.015 ± 0.010 (0.381 ± 0.254)	0.040 (1.02)	0.050 (1.27)	0.020 (0.50)
	0.001 to 0.0019				0.041 ± 0.010 (1.04 ± 0.254)			
WSLP120618	0.002 to 0.0059	0.126 ± 0.010 (3.20 ± 0.254)	0.063 ± 0.010 (1.60 ± 0.254)	0.025 ± 0.010 (0.635 ± 0.254)	0.025 ± 0.010 (0.635 ± 0.254)	0.062 (1.57)	0.070 (1.78)	0.030 (0.76)
	0.006 to 0.012				0.020 ± 0.010 (0.508 ± 0.254)			

WELDED CONSTRUCTION 1206



- Resistive element:
 solid metal nickel-chrome
 or manganese-copper
 alloy resistive element with
 low TCR (< 20 ppm/°C)
- 2) Plated terminal: Solid copper, 100 % Sn (100 μ^{H} min.) with 100 % Ni (20 μ^{H} min.) under layer finish
- 3) Terminal / element weld
- 4) Silicone coating with ink print

CLAD CONSTRUCTION 0805




- 1) Resistive element: Ni-Cr
- 2) Terminal: Solid copper, 100 % Sn (100 μ" min.) with 100 % Ni (20 μ" min.) under layer finish
- 3) Terminal to element weld
- High temperature encapsulant:
 "siliconized polyester"
 coating material


Revision: 13-Apr-18 2 Document Number: 30298



DERATING



PULSE CAPABILITY



www.vishay.com/resistors/power-metal-strip-calculator

PERFORMANCE				
TEST	CONDITIONS OF TEST	TEST LIMITS		
Thermal shock	-55 °C to +150 °C, 1000 cycles, 15 min at each extreme	± 0.5 %		
Short time overload	0805: 5x rated power for 5s	± 1.0 %		
Short time overload	1206: 3x rated power for 5 s	± 1.0 %		
Low temperature operation	-65 °C for 24 h	± 0.5 %		
High temperature exposure	1000 h at +170 °C	± 1.0 %		
Bias humidity	+85 °C, 85 % RH, 10 % bias, 1000 h	± 0.5 %		
Mechanical shock	100 g's for 6 ms, 5 pulses	± 0.5 %		
Vibration	Frequency varied 10 Hz to 2000 Hz in 1 min, 3 directions, 12 h	± 0.5 %		
Load life	1000 h at 70 °C, 1.5 h "ON", 0.5 h "OFF"	± 1.0 %		
Resistance to solder heat	+260 °C solder, 10 s to 12 s dwell, 25 mm/s emergence	± 0.5 %		
Moisture resistance	MIL-STD-202, method 106, 0 % power, 7b not required	± 0.5 %		

PACKAGING							
MODEL		REEL					
MODEL	TAPE WIDTH	DIAMETER	PIECES/REEL	CODE			
WSLP080518	8 mm/punched paper	178 mm/7"	5000	EA			
WSLP120618	8 mm/punched paper	178 mm/7"	4000	EA			

Notes

- Embossed carrier tape per EIA-481-2
- Additional packaging details at <u>www.vishay.com/doc?20051</u>



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.