# HCU, HCZ, HCE Series

Vishay Draloric

RoHS

COMPLIANT

## Ceramic Singlelayer DC Disc Capacitors, 3 kV<sub>DC</sub> General Purpose



www.vishay.com

QUICK REFERENCE DATA				
DESCRIPTION	VALUE			
Ceramic Class	1	2		
Ceramic Dielectric	N750, Y5T, Y5U			
Voltage (V <sub>DC</sub> )	3000			
Min. Capacitance (pF)	10	68		
Max. Capacitance (pF)	330	10 000		
Mounting	Radial			

#### MARKING

Marking indicates, capacitance, tolerance code, and rated voltage.

#### **OPERATING TEMPERATURE RANGE**

-40 °C to +85 °C

### **TEMPERATURE CHARACTERISTICS**

Class 1	N750 (U2J)
Class 2	Y5S, Y5U, Y5V

### SECTIONAL SPECIFICATIONS

Climatic category (according to EN 60068-1): 40/085/21

### FEATURES

- High capacitance in small sizes
- Low losses
- Wide range of different lead styles
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

#### **APPLICATIONS**

- Lighting ballasts
- SMPS

#### DESIGN

The capacitors consist of a ceramic disc which is silver plated on both sides. Connection leads are made of tinned copper having diameters of 0.6 mm or 0.8 mm.

The capacitors may be supplied with straight or kinked leads having a lead spacing of 7.5 mm.

Coating is made of blue colored flame retardant epoxy resin in accordance with UL 94 V-0.

#### CAPACITANCE RANGE

10 pF to 22 nF

### **RATED VOLTAGE**

 $3 \text{ kV}_{\text{DC}}$ 

#### **DIELECTRIC STRENGTH**

5000 V<sub>DC</sub>, 2 s Component test

### INSULATION RESISTANCE AT 500 $V_{\text{DC}}$

 $\geq$  10 000 M $\Omega$  (60 s)

#### **TOLERANCE ON CAPACITANCE**

 $\pm$  10 %,  $\pm$  20 %

### **DISSIPATION FACTOR**

Class 1:  $C < 30 \text{ pF}: \left(\frac{100 \text{ pF}}{C} + 0.7\right) \times 10^{-4} \text{ max.} (1 \text{ MHz})$   $C \ge 30 \text{ pF}: \text{ max.} 0.1 \% (1 \text{ MHz})$ Class 2: max. 2.5 % (1 kHz)

1




# HCU, HCZ, HCE Series

Vishay Draloric

#### **DIMENSIONS** in millimeters

Revision: 16-Sep-14



		DODY		LEAD	LEAD	M(ID T) (1)	ORDERING CODI
CAPACITANCE (pF)	TOLERANCE (%)	BODY DIAMETER D <sub>max.</sub> (mm)	BODY THICKNESS S <sub>max.</sub> (mm)	SPACING <sup>(1)</sup> F (mm) ± 1 mm	DIAMETER <sup>(1)</sup> d (mm) ± 0.05 mm	WIDTH <sup>(1)</sup> V (mm) ± 0.5 mm	MISSING DIGITS SEE ORDERING CODE BELOW
N750 (U2J)	1	1	I	I			
10				. 10.0 .	0.6	1.3	HCU100KBC###K
15		7.0	4.0				HCU150KBC###K
22		7.0					HCU220KBC###K
33							HCU330KBC###K
47		8.0					HCU470KBC###K
68	± 10	9.0				1.4	HCU680KBC###K
82	]	10.0			0.8	1.6	HCU820KBC###K
100		10.0					HCU101KBC###K
150		11.0	4.4				HCU151KBC###K
220		15.0					HCU221KBC###K
330		17.0					HCU331KBC###K
Y5T (2D3)		1	•	•			
68					HCZ680#BC###K		
82			7.0		0.6	1.8	HCZ820#BC###K
100	1	7.0					HCZ101#BC###K
120							HCZ121#BC###K
150							HCZ151#BC###K
180							HCZ181#BC###K
220		8.0					HCZ221#BC###K
330							HCZ331#BC###K
470	± 10, ± 20	10.0	4.0	10.0			HCZ471#BC###K
680	1	10.0					HCZ681#BC###K
1000	1	11.0	1				HCZ102#BC###K
1200	1	45.0	15.0				HCZ122#BC###K
1500	1	15.0					HCZ152#BC###K
2200	1	17.0	1		0.8	2.0	HCZ222#BC###K
3300		21.0	1				HCZ332#BC###K
4700	1						HCZ472#BC###K
6800	1	25.0					HCZ682#BC###K

Document Number: 22153

2 For technical questions, contact: <u>slcap@vishay.com</u>

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

www.vishay.com

# HCU, HCZ, HCE Series

### Vishay Draloric

ORDERING INFORMATION							
		BODY	2021	LEAD	LEAD		ORDERING CODE
CAPACITANCE (pF)	TOLERANCE (%)	DIAMETER D <sub>max.</sub> (mm)	BODY THICKNESS S <sub>max.</sub> (mm)	SPACING <sup>(1)</sup> F (mm) ± 1 mm	DIAMETER <sup>(1)</sup> d (mm) ± 0.05 mm	V (mm) ± 0.5 mm	MISSING DIGITS SEE ORDERING CODE BELOW
Y5U (2E3)							
470		7.0					HCE471MBC###KR
680		8.0			0.6	2.0	HCE681MBC###KR
1000		9.0 ± 20 15.0					HCE102MBC###KR
1500			11.0				HCE152MBC###KR
2200	± 20		4.0	10.0			HCE222MBC###KR
3300							HCE332MBC###KR
4700		17.0			0.8	2.2	HCE472MBC###KR
6800		21.0			0.8		HCE682MBC###KR
10 000		25.0				2.5	HCE103MBC###KR

#### Note

SHAY

<sup>(1)</sup> Standard lead configuration, other lead spacing and diameter available on request

ORDERING CODE							
#	7 <sup>th</sup> digit	Capacitanc	e tolerance	± 10 % = K, ± 20	0 % = M		
###	10 <sup>th</sup> to 12 <sup>th</sup> digit	Lead config	guration	see "General Inf	ormation"		
Example	HCE	152	м	BC	DD0	К	R
	Series	Capacitance value	Tolerance code	Voltage code	Lead configuration	Internal code	RoHS compliant

MARKING	
68p k 3 kV 2	
HCU 10 pF to	150 pF HCU 220 pF to 330 pF
HCZ 68 pF to	1.0 nF HCZ 1.2 nF to 6.8 nF
HCE 470 pF to	

RELATED DOCUMENTS				
General Information	www.vishay.com/doc?22001			



Vishay

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.