

8

7

6

5

4

3

2

1

NOTES: UNLESS OTHERWISE SPECIFIED.





1 MATERIAL: CRS 18 AWG (.05 THICK) OR EQUIV.

2 FINISH: ZINC PLATE PER ELGAR SPEC 1006906-22.

3. BREAK AND DEBURR SHARP CORNERS AND EDGES.

4 IDENTIFY PER ELGAR SPECIFICATION 1006905 LOCATE APPROXIMATELY WHERE SHOWN

REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED
	01	PILOT REL PER DRN PR4323	2/21/02	C. PEREA
	02	REVISED PER ECN N050340	5/23/05	G. STAPP
	03	REVISED PER ECN N060034	6/20/06	G. STAPP



SEE SHEET 2 FOR DETAILED LAYOUT

-01

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		CONTRACT NO.		ELGAR		
DECIMALS	FRACTIONS	ANGLES	FIRST MADE FOR:			
.XX ± .03	± 1/32	± 1/2°	APPROVAL	DATE	ENCLOSURE, OUTPUT POWER - DCS	
.XXX ± .010			DRAWN	A. BIGORNIA		2/21/02
DO NOT SCALE THIS DRAWING			CHECKED	C. PEREA		2/21/02
			ENGINEER	D. DEVEL		2/21/02
NEXT ASSY.	DCS	MATERIAL:	QA-REL			
APPLICATION		1				
THE INFORMATION DISCLOSED HEREIN WAS ORIGINATED BY AND IS THE PROPERTY OF ELGAR CORPORATION, AND EXCEPT FOR RIGHTS EXPRESSLY GRANTED TO THE UNITED STATES GOVERNMENT, ELGAR CORPORATION RESERVES ALL PATENT, PROPRIETARY, DESIGN, USE, SALE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.		FINISH:				
		2				
SIZE	CODE IDENT. NO.	DWG. NO.	REV			
D	25965	9362219	03			
SCALE	1/1	SHEET 1 OF 2				

8

7

6

5

4

3

2






1

8 7 6 5 4 3 2 1

REVISIONS				
ZONE	REV	DESCRIPTION	DATE	APPROVED
		SEE SHEET 1		

D
C
B
A

D
C
B
A



8 7 6 5 4 3 2 1

SIZE	CODE IDENT. NO.	DWG. NO.	REV
D	25965	9362219	03
SCALE	1/1		SHEET 2 OF 2