

Request a Sample

Customer Specification PART NO. 3469C

Construction

				Diameters (In)		
1) Component 1		9 X 1 COND	9 X 1 COND			
a) Conductor		28 (7/36) AWG	28 (7/36) AWG TC		0.015	
b) Insulation		0.010" Wall, No	0.010" Wall, Nom. PVC, Semi Rigid		0.035	
(1) Color Code		Alpha Wire Cold	Alpha Wire Color Code D			
Cond	Color	Cond	Color	Cond	Color	
1	BLACK	4	GREEN	7	BROWN	
2	RED	5	ORANGE	8	YELLOW	
3	WHITE	6	BLUE	9	VIOLET	
2) Cable Assembly		9 Components	9 Components Cabled			
a) Twists:		6.9 Twists/foot (6.9 Twists/foot (min)			
3) Shield:		Alum/Mylar Tap	Alum/Mylar Tape, 25% Overlap, Min.			
a) Foil Direction		Foil Facing Out	Foil Facing Out			
b) Drain Wire		28 (7/36) AWG	28 (7/36) AWG TC			
c) Braid		TC,65% Covera	TC,65% Coverage, Min.			
4) Jacket		0.035" Wall, No	0.035" Wall, Nom.,PVC		0.223 (0.237 Max.)	
a) Color(s)		SLATE	SLATE			
b) Print		SHIELDED 75C LLXXXXXX CSA * = Factory Code	ALPHA WIRE-* P/N 3469C 9C 28 AWG SHIELDED 75C (UL) TYPE CL2 OR AWM 2464 LLXXXXXX CSA TYPE CMG FT4 CE ROHS * = Factory Code [Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]			

Applicable Specifications

1) UL	AWM/STYLE 2464	80°C / 300 V _{RMS}
	CL2	75°C
	VW-1	
2) CSA International	СМС	60°C
	FT4	
3) CE:	EU Low Voltage Directive 2006/95/EC	

Environmental

1) CE: EU Directive 2011/65/EU(RoH	S2), EU Directive 2015/863/EU (RoHS3):
	This product complies with European Directive 2011/65/EU (RoHS Directive) of the European Parliament and of the Council of 8 June 2011 and the amending Directive 2015/863/EU of 4 June 2015. No Exemptions are required for RoHS Compliance on this item. Consult Alpha Wire's web site for RoHS C of C.
2) REACH Regulation (EC 1907/2006):
	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see Alpha's REACH SVHC Declaration.
3) California Proposition 65:	Exempt from warning labels based on the Consent Judgment. Please see Alpha's CA Prop 65 Statement for more information.

Properties

Physical & Mechanical Properties				
1) Temperature Range	-20 to 80°C			
2) Bend Radius	10X Cable Diameter			
3) Pull Tension	16.4 Lbs, Maximum			
Electrical Properties	(For Engineering purposes only)			
1) Voltage Rating	300 V _{RMS}			
2) Capacitance	25 pf/ft @1 kHz, Nominal Conductor to Conductor			
3) Ground Capacitance	45 pf/ft @1 kHz, Nominal			
4) Inductance	0.22 μH/ft, Nominal			
5) Conductor DCR	66 Ω/1000ft @20°C, Nominal			
6) OA Shield DCR	6.2 Ω/1000ft @20°C, Nominal			

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 1000 FT	12 x 10 x 5 Continuous length
b) 500 FT	12 x 4.5 x 3.5 Continuous length
c) 100 FT	6.5 x 4 x 2.5 Continuous length
	[Spool dimensions may vary slightly]

www.alphawire.com

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207 Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE - CONFIDENTIAL AND PROPRIETARY

Notice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document. ©2013 ALPHA WIRE - all rights reserved.



EU/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: 3469C

3469C, RoHS-Compliant Commencing With 3/1/2005 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3) The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item**. Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014.

•			
Substance	Maximum Control Value		
Lead	0.1% by weight (1000 ppm)		
Mercury	0.1% by weight (1000 ppm)		
Cadmium	0.01% by weight (100 ppm)		
Hexavalent Chromium	0.1% by weight (1000 ppm)		
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)		
Polybrominated Diphenyl Ethers (PBDE) ,			
Including Deca-BDE	0.1% by weight (1000 ppm)		
Bis(2-ethylhexyl) phthalate (DEHP)	0.1% by weight (1000 ppm)		
Butyl benzyl phthalate (BBP)	0.1% by weight (1000 ppm)		
Dibutyl phthalate (DBP)	0.1% by weight (1000 ppm)		
Diisobutyl phthalate (DIBP)	0.1% by weight (1000 ppm)		

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

Dave Watson, Director of Engineering & QA

Alpha Wire

711 Lidgerwood Ave. Elizabeth, NJ 07207 Tel: 1-908-925-8000 9/12/2019