

Conductor marking collar - LBHZ 2/WH:UNBEDRUCKT - 1013575


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marking collar, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: slide-on, cable diameter range: 1.5 ... 3.2 mm, lettering field size: 4.5 x 10 mm, Number of individual labels: 10



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| GTIN |  4 017918 013851 |
| GTIN | 4017918013851 |
| Weight per Piece (excluding packing) | 1.100 g |
| Custom tariff number | 39269097 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|----------------|-------------------|
| Length (b) | 10 mm |
| Width (a) | 4.5 mm |
| Height (c) | 6 mm |
| Cable diameter | 1.5 mm ... 3.2 mm |

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

General

| | |
|--|--------------------------------|
| Note | Can be labeled with CMS |
| Color | white |
| Type | Card form |
| Components | free from silicone and halogen |
| Flammability rating according to UL 94 | V2 |

Conductor marking collar - LBHZ 2/WH:UNBEDRUCKT - 1013575

Technical data

General

| | |
|-------------------------------------|-----------------------------|
| Material | PA |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 10 |
| Number of individual labels per row | 10 |
| Marking mounting type | slide-on |

Standards and Regulations

| | |
|--|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V2 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27061700 |
| eCl@ss 4.1 | 27061700 |
| eCl@ss 5.0 | 27400400 |
| eCl@ss 5.1 | 27400400 |
| eCl@ss 6.0 | 27400400 |
| eCl@ss 7.0 | 27400401 |
| eCl@ss 8.0 | 27400401 |
| eCl@ss 9.0 | 27400401 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001530 |
| ETIM 6.0 | EC001530 |
| ETIM 7.0 | EC001530 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39131504 |
| UNSPSC 18.0 | 39131504 |
| UNSPSC 19.0 | 39131504 |
| UNSPSC 20.0 | 39131504 |
| UNSPSC 21.0 | 39131504 |

