



LED Filament Cookerhood E14



Product Overview

LED Filament Lamps operate direct from the mains, without the need for a transformer, making them quick and easy to install, simple to operate and lowering installation and user costs.

Features

- More eco-valued.
- Excellent color rendering and consistency
- Reliable construction

Safety and Maintenance

- Switch off supply before installing or removing lamp.
- Allow to cool before handling.
- Do not use in application where voltage is unable
- This is a glass product, handle with care

Specifications – E14 (boxed), E14 (blister 2pk)

| | | |
|--------------------------------|------------------|-------------------|
| SKU | S13563 | S13564 |
| Lamp | E14 (boxed) | E14 (blister 2pk) |
| Nominal Power (W) | 3.8W | 3.8W |
| Voltage | 220-240Vac 50Hz | 220-240Vac 50Hz |
| Nominal Luminous Flux (lm) | 420 | 420 |
| CCT (K) | 3000K warm White | 3000K warm White |
| Nominal Lifetime (h) | 15000 | 15000 |
| Dimmable | No | No |
| Switching Cycles | 15000 | 15000 |
| Warm-up time to 60% (S) | instant | instant |
| Length (mm) | 80 | 80 |
| Diameter (mm) | 28 | 28 |
| Mercury (mg) | 0 | 0 |
| Clean-up instructions | See website | See website |
| Retrofit Yes | | |
| Equivalent Wattage (W) | 35 | 35 |
| Rated Power (W) | 3.8 | 3.8 |
| Rated Luminous Flux (lm) | 420 | 420 |
| Rated Lifetime (h) | 15000 | 15000 |
| Power Factor | >0.4 | >0.4 |
| Rated Peak Candelas (cd) | | |
| Lumen Maintenance Factor at | | |
| Nominal Lifetime | 15000 | 15000 |
| CRI | >80 | >80 |
| Start Time (s) | instant | instant |
| Ambient Temperature Range (°C) | -20 to 40 | -20 to 40 |

Energy Label – E14 (boxed), E14 (blister 2pk)


| | | |
|--------------------------------|--------------|--------------|
| Energy Class | A++ | A++ |
| Energy Consumption (kWh/1000h) | 4.00 (3.8)* | 4.00 (3.8)* |

* The kWh/1000h value published on the energy label is required to be rounded up to an integer according to the EU implementing directive on Energy Labelling. The value to 2 decimal places is given for reference

Product Markings – E14 (boxed), E14 (blister 2pk)

| | | |
|-------------------|-----------------|-----------------|
| Voltage | 220-240Vac 50Hz | 220-240Vac 50Hz |
| Nominal Power (W) | 3.8 | 3.8 |
| Current (mA) | | |
| CE Mark | Yes | Yes |
| WEEE Mark | Yes | Yes |
| Batch Code | Yes | Yes |

Dimensions



Photometric Information

3000K

